





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	FIBER SIZE (MICRONS)	FERRULE CAP COLOR	WEIGHT
FJJSMM5C**	62.5	BLACK	.21 LB/10 PCS (93.5 g/10 PCS)
FJJSMM50C**	50	ORANGE	.21 LB/10 PCS (93.5 g/10 PCS)



- NOTES:
- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
  - SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
  - DIMENSIONS IN PARENTHESES ARE IN METRIC.
  - MATERIAL;
    - BOOTS: ELASTOMER
    - JACK COVER: PC/ABS
    - CRIMP SLEEVE: BRASS
    - FERRULE: CERAMIC
    - JACK HOUSING: PC/ABS
    - JACK DUST CAP: ELASTOMER



										OPTI-JACK MULTIMODE PRE-POLISHED CRIMP OPTICAL FIBER CONNECTOR			
										CUSTOMER DRAWING			
										 <b>PANDUIT</b> ™ CORP. TINLEY PARK, ILL 60477			
										ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) (.XXX)±.010 (0.3) (.XX)±.03 (0.8) ANGLES		DRAWING FILENAME M00805AB_DC_00B.prt SCALE NONE	
										THIRD ANGLE PROJECTION		PART NO. FJJSMM5C** FJJSMM50C**	
										DRAWN BY MC DATE 08-11-00 CHECKED JAW		REVIEW DRAWING NUMBERS DRAWING NO. 00805-05 SIZE A	
1	04-27-05	MYW		RELEASED TO PRODUCTION	00805-05								
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	CHK'D	JAW		