



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
SRBM19BLY	.48 LB/EACH PC (221.9 g/EACH PC)


NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PART INCLUDES:
1- STRAIN RELIEF BAR
1- #12-24 SCREW KIT
1- M6 SCREW KIT
6- HOOK AND LOOP CABLE TIE (HLS1.5-X0)



MODEL FILENAME	M00741DI_SRB_00.PRT	SIZE
DRAWING FILENAME	M02479BA_DC027_00A.PRT	A

STRAIN RELIEF BAR MANAGER
CUSTOMER DRAWING

 PANDUIT ™ CORP. TINLEY PARK, ILL 60477	I.I. NUMBER	N/A
	PRODUCT SPEC	N/A
 THIRD ANGLE PROJECTION	WORK INSTRUCTION	N/A
	SCALE	NONE
DRAWN BY JsP	MATERIAL:	PART NO. SRBM19BLY
DATE 4-18-06	16 GAGE C.R.S.	DRAWING NO. 02479-027
CHK'D		

R	4-18-06	JsP		RELEASED TO PRODUCTION	02479-027				
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH