











INSTALLATION INSTRUCTIONS T-PMPI-277-PC

© PANDUIT Corp. 2007

	RGS134B-1	RGRB19CN
	1	-
Cage Nut Grounding Strip		
	3	-
Strip Clip		
	-	2
Universal Grounding Sticker		
	-	1
19" Universal Ground Bar		
	1	-
Cleaning Pad		
	8	4
12-24 HDW		
	3	2
Cage Nut Stud HDW		
	1	1
AntiOx		



All torque values are based on a maximum Equipment Rail coating of .003 inches.

<p>For Instructions in Local Languages and Technical Support: http://www.panduit.com/resources/install_maintain.asp</p>	 www.panduit.com	<p>E-mail: cs@panduit.com Fax: (815)485-5839</p>
--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	---------------------------------------------------------------------------------------------------------------------------------------------	---------------------------------------------------------------------------------------------------