





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART#	DESCRIPTION	WEIGHT*
CJS688TGY	8 POSITION, 8 WIRE SHIELDED MODULE WITH INTEGRAL SHIELD. TERMINATION CAP IS COLOR CODED FOR T568A AND T568B WIRING SCHEMES.	3.314 LB/100 PCS (1503g/100 PCS)



- NOTES:
1. WHITE WIRE CAP DESIGNATES CATEGORY 6 PERFORMANCE.
 2. MATERIAL:
MODULE HOUSING-ABS
NOMINAL WALL THICKNESS .078(2.0).
WIRE CAP-PC
 3. ALL TX6 PLUS, 8 POSITION, 8 WIRE JACK MODULES ARE UNIVERSAL IN DESIGN. THEY ACCEPT SIX AND EIGHT POSITION MODULAR PLUGS WITHOUT DAMAGE.
 4. DIMENSIONS IN PARENTHESES ARE IN METRIC.
 5. .187 x .010" GROUNDING TAB PROVIDED AS OPTIONAL CONDUCTIVE PATH FOR GROUNDING.
- *WEIGHT IS APPROXIMATE



MODEL FILENAME M01874A1_10GTX_SHLD_ASSY_03		SIZE A
DRAWING FILENAME M02479NS_DC357_00B.prt		
TITLE TX6 PLUS SHIELDED JACK MODULE CUSTOMER DRAWING		
 PANDUIT ™ CORP. TINLEY PARK, ILL 60477		I.I. NUMBER
 THIRD ANGLE PROJECTION		PRODUCT SPEC
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ±.010(.3) (.XX) ±.03(.8) ANGLES ±		WORK INSTRUCTION
DRAWN BY AFW		SCALE FULL
DATE 3-11-06	REVIEW DRAWING NUMBERS	PART NO. CJS688TGY
CHK'D CEF		DRAWING NO. 02479-357

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
I	10-9-06	MDJR		UPDATED MODEL TO REV. 03.	02479-357				
R	3-11-06	MDJR	CEF	ADDED RoHs P/N	02479-357	CEF	CEF		CEF