



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	WEIGHT
DPA245E88TGY	1.26 lb (571.53 g)



NOTES:

1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AS WELL AS OPTIONAL ICONS.
2. MATERIAL:  
PANEL HOUSING: STEEL  
RJ45 MODULES: THERMOPLASTIC RESIN UL94V-0  
PUNCHDOWN BLOCKS: THERMOPLASTIC RESIN UL94V-0  
BEZEL ASSEMBLY: THERMOPLASTIC RESIN UL94H-B  
RETENTION CAP:  
THERMOPLASTIC RESIN UL94V-0
3. 24 PORT ANGLED PATCH PANEL 8 POSITION 8 WIRE.
4. THE PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
5. FOUR (4) 12-24 X 1/2" ROUND HEAD SCREWS AND (4) M6x1x15MM METRIC SCREWS ARE PROVIDED FOR FASTENING TO RACKS.
6. DIMENSIONS IN BRACKETS ARE IN METRIC.
7. USE 110 STYLE TERMINATION TOOL FOR PUNCHDOWN.
8. RETENTION CAPS (ONE PER CONNECTOR) PROVIDED FOR SNAP-IN ON TERMINATED CONNECTORS.



CID\*\*-C & CIP\*\*-C, PHONE OR DATA ICON LOCATES HERE. IDENTIFIES INDIVIDUAL PORT. OPTIONAL, NOT SUPPLIED.

MODEL FILENAME	M02088AC/04	SIZE	A
DRAWING FILENAME	M02479JH_DC244/00B		
DP5E 24 PORT ANGLED PATCH PANEL CUSTOMER DRAWING			
	PANDUIT <sup>TM</sup> CORP. TINLEY PARK, ILL 60477	I.I. NUMBER	
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.		PRODUCT SPEC	
DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.005 (.XX) ±.01 ANGLES ± 1°		WORK INSTRUCTION	
THIRD ANGLE PROJECTION		SCALE .25 : 1	
DRAWN BY LZ		PART NO. SEE CHART	
DATE 3-4-06		DRAWING NO. 02479-244	
CHK'D CEF			

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
I	4-14-10	BJN	KAA	A. CORRECTED METRIC WEIGHT	02479-244	MBVE	MBVE		
R	3-4-06	LZ	CEF	RELEASED TO PRODUCTION	02479-244	CEF		CEF	CEF