


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
F06CB	.44 LB/10 PCS (220 g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. DIMENSIONS IN PARENTHESES ARE IN METRIC.
3. MATERIAL:
TUBING: HYTREL
BASE, COVER AND BREAKOUT BLOCK: ABS
4. THE BREAKOUT BLOCK TUBE ASSEMBLY WILL ROUTE 250 MICRON FIBERS INTO INDIVIDUAL, 900 MICRON COLOR CODED BUFFERED TUBES.
5. TALC POWDER IS PROVIDED TO FACILITATE THREADING OF THE 250 MICRON FIBERS THROUGH THE COLORED TUBING.
6. THE TUBING WILL WITHSTAND A MINIMUM BEND RADIUS OF .51 INCHES (1.3 CM) WITHOUT ANY BREAKS OR KINKS.
7. DOUBLE-SIDED TAPE WILL IS PROVIDED FOR SECURING THE BASE.
8. THE BASE HAS A METAL RECTANGLE CLIP TO HOLD THE LOOSE TUBE IN PLACE AND WILL ACCEPT INDUSTRY STANDARD LOOSE TUBE FROM 2.00 MM TO 3.20 MM IN DIAMETER.
9. THE BASE HAS A CAVITY FOR HOLDING AND LOCKING THE BREAKOUT BLOCK IN PLACE.
10. TUBING COLOR CODE PER BELLCORE STANDARDS:
1/BLUE, 2/ORANGE, 3/GREEN, 4/BROWN, 5/SLATE, 6/WHITE
11. TUBE LENGTH IS 36" ± 1.00 ".

CAD FILENAME/LAYERS

M00526AB_DC_00A.PRT

PANDUIT

CORP. TINLEY PARK, ILLINOIS

FIBER OPTIC 6 TUBE FAN-OUT KIT
(F06CB) CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) \pm (.XXX) \pm .010(.3)
(.XX) \pm .03(.8) ANGLES \pm

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
JBA

MAT'L:

SCALE

NONE

DATE

6-29-99

SEE NOTES

DRAWING NO.

00526-04

DWG

SIZE

R	6-29-99	JBA		RELEASED TO PRODUCTION.	00526-04				
REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP	