

## Features

- **Weather-Resistant Wall-Mount Design, Type-3R**
- **Rugged Cast-Aluminum Enclosure with Epoxy Safety Yellow Finish**
- **Telephone Line Powered, (No Battery or External Power Required for Telephone Operation)**
- **Large "Palm" Activation HELP Pushbutton For Emergency Call**
- **Standard or SMART Operation**
- **Auto Answer (with Silent Monitoring)**
- **(2) Programmable Auxiliary Outputs for Peripheral Equipment Control**
- **Operating Range of -20°C to +60°C**
- **Call Received When Lit L.E.D.**
- **Voice Annunciation Option**
- **Extreme Cold Weather Option (-40°C)**
- **3-Number Rollover**
- **UL/CSA 60950 Compliant**
- **FCC Part 68 Certified**
- **ADA Compliant**
- **Monitored by TMA (Telephone Management Application) Software**



GAI-Tronics' RED ALERT® Emergency Telephones are designed to provide clear and reliable communications in almost any environment. The model 393AL-00x is considered to be Type-3R weatherproof compliant when installed on any flat surface.

The 393AL-00x RED ALERT® Emergency Telephones provide reliable two-way communications with the press of a single button and can be installed on any analog PSTN, PBX, PABX, or KSU network providing 24 V dc or 48 V dc line voltage with a minimum line current of 24 mA. **No external power is required for normal operation.**

The Model 393AL-00x is capable of providing two (2) auxiliary outputs for control of peripherals such as strobes, door / gate access, alarms, or lamps via local or remote activation. These outputs can be programmed for a variety of control parameters including telephone HELP button or remote DTMF activation. Each telephone can additionally be configured to automatically answer when called.

Each telephone is ADA compliant, with a "Call Received When Lit" L.E.D. providing visual indication that a call is active and a Braille HELP label.

Although each of these telephones will function as a standard Emergency Telephone, connecting a customer-provided, central computer equipped with GAI-Tronics' TMA (Telephone Management Application) software will allow them to operate in SMART (Self-Monitoring and Reporting Technology) mode. With TMA connected, each RED ALERT® telephone will be polled on a scheduled basis to report:

- **Line integrity**
- **Microprocessor health**
- **Stuck buttons**
- **Microphone integrity**
- **Speaker integrity**
- **Line interrupt (power failure)**
- **Low Battery (Voice Annunciation Option only)**

Additionally, each RED ALERT® Emergency Telephone is available with a user programmable Voice Annunciation option and/or an Extreme Cold Weather option (to -40°C).

No other telephone provides greater features, value, and reliability.

## Specifications

TMA compatibility profile type . . . . GTC SMART Hands-free

### Electrical

Audio Output. . . . . 1 kHz tone @  $87 \pm 3$  dB SPL  
@ 1 meter with 40 mA loop current

Battery Voltage (tip and ring) . . . . . 24 V dc or 48 V dc

Phone line requirements . . . . . Loop start, central office  
(CO), or Analog station port (PBX, PABX, or KSU)

Minimum loop current . . . . . 24 mA  
(35 mA recommended)

(2) Auxiliary outputs (Isolated solid state switch) . . . . .  
48 V dc @ 125 mA

28 V<sub>RMS</sub> ac @ 80 mA<sub>RMS</sub>

Signaling . . . . . DTMF 100 ms tone

Memory . . . . . Non-volatile EEPROM

### Mechanical

Operating Temperature Range:

-003 and -004 Models: -40° F to +140° F (-40° C to +60° C)

-001 and -002 Models: -4° F to +140° F (-20° C to +60° C)

Relative Humidity. . . . . to 95%, no condensation

Construction:

Enclosure Construction . . . . . Cast Aluminum,  
epoxy finish, painted safety yellow

Dimensions. . . . . 9.5 H x 8.0 W x 4.0 D inches  
(241.3 x 203.2 x 101.6 mm)

Weight. . . . . 7.8 lbs. (3.5kg)

### Approval Standards

Safety of Information Technology Equipment: UL/CSA 60950

Enclosures for Electrical Equipment . . . . . UL 50, Type 3R

### 47 CFR Part 68

Certification Number . . . . . US: ADGTE05BGTC2010

Ringer Equivalent Number . . . . . .5B

Network connection (USOC) . . . . . RJ11

### IC information (Canada)

IC Certification Number . . . . . 882B-GTC 2010

Ringer Equivalent Number . . . . . .5B

Connection Method . . . . . CA11A

## Model Chart

Model	Description
393AL-001	Weatherproof, Surface-mount, One-Button, Emergency Telephone, Cast Aluminum Enclosure, Yellow Epoxy Finish
393AL-002	Weatherproof, Surface-mount, One-Button, Emergency Telephone, Cast Aluminum Enclosure, Yellow Epoxy Finish with Voice Annunciation Option
393AL-003	Weatherproof, Surface-mount, One-Button, Emergency Telephone, Cast Aluminum Enclosure, Yellow Epoxy Finish with Extreme Cold Weather Option
393AL-004	Weatherproof, Surface-mount, One-Button, Emergency Telephone, Cast Aluminum Enclosure, Yellow Epoxy Finish with Voice Annunciation Option and Extreme Cold Weather Option
12509-037	TMA Application Package (includes single line transceiver, security key, interconnecting cables, software CD, and manual)
12509-036	TMA Line Expansion Kit; one required for each additional monitored line...8 max. (includes single line transceiver, interconnecting cables, and manual)
233-001	Security Screwdriver

