





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT	FERRULE TYPE
FSCM2.0** FSCS2.0BU	.090 LBS/10 PCS. (40.8 G/10 PCS.)	ZIRCONIA (CERAMIC)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. MULTIMODE CONNECTORS (FSCM2.0\*\*) ACCEPT 50/125 OR 62.5/125  $\mu$ m MULTIMODE GLASS OPTICAL FIBER.
3. SINGLEMODE CONNECTORS (FSCS2.0BU) ACCEPT 9/125  $\mu$ m SINGLEMODE GLASS OPTICAL FIBER.
4. COMPLIES WITH THE FIBER OPTIC PERFORMANCE REQUIREMENTS AS SPECIFIED IN TIA/EIA 568-A AND B.3.
5. COMPLIES WITH FOCIS-3 (TIA/EIA 604-3).
6. DIMENSIONS IN PARENTHESIS ARE METRIC.

										FIBER OPTIC SC CONNECTOR	
										CUSTOMER DRAWING	
											 TINLEY PARK, ILL 60477
										 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.  DIMENSIONAL TOLERANCES ARE: (.X) ±.03    (.XXX) ±.005 (.XX) ±.01    ANGLES ± 1°
											DRAWING FILENAME MO1069AD_DC_00A
											SCALE NONE
										DRAWN BY JH	PART NO.    FSCM2.0** FSCS2.0BU
										DATE 05-23-06	DRAWING NO.    01069-20
R	05-30-06	JH		RELEASED TO PRODUCTION							SIZE A
REV	DATE	BY	CHK	DESCRIPTION		ECN	-	R	CUST	SUP	OTH