


PANDUIT
PART NUMBER



FMTPRR6

APPROXIMATE PRODUCT DIMENSIONS

2.0 DIA. X 0.8 inches
[51 DIA. X 20 mm]



1. THIS PRODUCT FITS PANDUIT REEL CLEANERS FMTPFCT AND FMTPMCT.
2. EACH REPLACEMENT REEL PROVIDES ENOUGH CLEANING CLOTH FOR APPROXIMATELY 400 CLEANINGS.
3. THE CLEANING CLOTH IS AN ULTRA CLEAN MICRO-FIBER CLOTH THAT CAPTURES DEBRIS AND OTHER CONTAMINATION, DOES NOT FRAY, AND DOES NOT LEAVE ANY FIBROUS MATERIALS ON THE FERRULE ENDFACES BEING CLEANED.
4. THE CLEANING CLOTH DOES NOT REQUIRE THE USE OF ADDITIONAL WET CLEANING AGENTS.
5. OPERATING TEMPERATURE: 0 TO 40 °C
6. STORAGE TEMPERATURE: -20 TO 60 °C
7. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

										CLEANING REEL REFILL FOR REEL CLEANING TOOL
										CUSTOMER DRAWING
										 <p>PANDUITTM CORP. TINLEY PARK, ILL 60477</p>
										 THIRD ANGLE PROJECTION
										ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED.
										DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ± .010 (.0.3) (.XX) ± .03 (.0.8) ANGLES
										DRAWING FILENAME M01893ZL_DC_00A.prt
										SCALE NONE
										PART NO. FMTPRR6
R	01-05-07	MC		RELEASED TO PRODUCTION	01893-54					DRAWING NO. 01893-54
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH	CHK'D	SIZE A