




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT PART NO.	WEIGHT
P110B300-X	1.26 LB/EACH 570 g/EACH

NOTE:

1. DIMENSIONS ARE NOMINAL UNLESS OTHERWISE SPECIFIED.
2. TOOTH GEOMETRY IN WIRE SEPARATOR SIMPLIFIED FOR DWG CLARITY.
3. WIRE SEPARATOR TEETH MARKED ACCORDING TO 25-PAIR TIP COLOR SCHEME.
4. APPEARING ON TOP SURFACE: "PANDUIT", PART#, AND QC#.
5. DIMENSIONS IN [] ARE IN METRIC UNITS.



MODEL FILENAME B50000LJ_CD10652_07.PRT		SIZE A
DRAWING FILENAME V:9507566/B50000LJ_DC_06A.PRT		
PAN-PUNCH 110 PUNCHDOWN SYSTEM 300 PAIR BASE WITHOUT LEGS CUSTOMER DRAWING		
 PANDUIT ™ CORP. TINLEY PARK, ILL 60477	I.I. NUMBER	
	PRODUCT SPEC/ PKG SPEC	
 THIRD ANGLE PROJECTION	ASSY METHOD/ TEST METHOD	
	SCALE 3/8=1	
DRAWN BY BAP	REVIEW DRAWING NUMBERS	PART NO. P110B300-X
DATE 2-12-97		DRAWING NO. KA-10494
CHK'D UNK	MATERIAL ENGINEERING THERMOPLASTIC UL94 V-0	

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
I	7-09-07	MDJR	EJH	A. UPDATED DRAWING WITH NEW TITLE BLOCK AND DELETED SHEET 2.	KA-10494		REGA		
R	2-12-97	BAP	UNK	RELEASED TO PRODUCTION	KA-10494		UNK		