

PANDUIT* PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	G in (mm)	H in (mm)	MAX. PANEL THICKNESS in (mm)	MIN. LOOP TENSILE lbs (N)	CROSS SECTION	WEIGHT 100 pcs lbs (g)
	MIN. in (mm)	MAX. in (mm)												
PLP1S	.06 (1.5)	1.00 (25.4)	.050 (1.3)	.180 (4.6)	.300 (7.6)	.354 (9.0)	.370 (9.4)	5.3 (135)	.330 (8.4)	.250 (6.4)	.125 (3.2)	50 (222)	STANDARD	.24 (109)
PLP1.5S	.06 (1.5)	1.50 (38.1)	.050 (1.3)	.180 (4.6)	.300 (7.6)	.354 (9.0)	.370 (9.4)	6.7 (170)	.330 (8.4)	.250 (6.4)	.125 (3.2)	50 (222)	STANDARD	.29 (132)
PLP2S	.06 (1.5)	1.75 (44.5)	.050 (1.3)	.180 (4.6)	.300 (7.6)	.354 (9.0)	.370 (9.4)	7.88 (200)	.330 (8.4)	.250 (6.4)	.125 (3.2)	50 (222)	STANDARD	.32 (145)

*1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
2) THESE PARTS ARE RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.
3) SEE DRAWING SS-26888(A) FOR PLP1.51.

PANDUIT CORP. TINLEY PARK, ILLINOIS

STRAP, PUSH MOUNT - PLP

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .1(2.5)(.XXX) ± .020 (.51)
(.XX) ± .02(.5) ANGLES ± -----

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
RAM

DATE
4-27-93

CHK'D	HVP
-------	-----

MAT'L:	
--------	--

NYLON 6.6

SCALE

DRAWING NO.
SS-26803

DWG
A
SIZE

---	----	---		CHANGED NOMINAL HOLE DIA TO .250, WAS .252	-----	---				
---	----	---		ADDED WEIGHT COLUMN	-----	---				
6	1/22/04	JABO		CHANGED FORMAT FOR CONSISTENCY - SEE ECN FOR DETAILS	26803	6				
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		