



Model NV-213A Video Transceiver



Features:

- Full-motion CCTV video at distances up to 750ft (225m) when used with any passive NVT transceiver or hub
- Up to 3,000 feet (1,000 m) with a DigitalEQ™ Hub or active receiver
- Up to 1,500 feet (460m) shall be supported by any NVT StubEQ™ Hub
- Up to ten NV-213As may be rack mounted using the NV-RM8/10 rack panel kit
- Mini-coax pigtail supports in-camera mounting in most dome cameras
- No power required
- Exceptional interference rejection
- Built-in transient protection with separate ground connection
- Supports “up-the-coax” type control signal up to 750ft (225m)
- Limited lifetime warranty

The NVT Model NV-213A Video Transceiver is a passive (non-amplified) device that allows the transmission of real-time monochrome or color video over Unshielded Twisted-Pair (UTP) telephone wire. Baseband (composite) signals of any type are supported.

The passive NV-213A is capable of delivering a fully equalized signal to the DVR when used with any Active NVT Receiver, yet is compatible with all of NVT's passive products for applications under 750ft (225m). The NV-213A Video Transceiver also incorporates transient protection.

The unparalleled interference rejection and low emissions of the NV-213A allow video signals to co-exist in the same wire bundle as telephone, datacom, or low-voltage power circuits. This allows the use of a shared or existing cable plant.

Network Video Technologies

4005 Bohannon Drive • Menlo Park, CA 94025 • USA
(+1) 650.462.8100 • FAX (+1) 650.326.1940
nvt.com • www.nvt.com/email




Model NV-213A

Video Transceiver

Technical Specifications

VIDEO DISTANCE RECOMMENDATIONS



VIDEO

Frequency response	DC to 10 MHz
Attenuation	0.5 dB typ
Common-mode / Differential-mode rejection	
15 KHz to 5 MHz	60 dB typ
Impedance	
Coax, male BNC	75 ohms
UTP, Screwless terminal block	100 ohms

POWER

No external power required

ENVIRONMENTAL

Ambient ambient temperature	-22 to +167 °F (-30 to +75 °C)
Humidity (non-condensing)	0 to 95%
Transient Immunity	per ANSI / IEEE 587 C62.41

WIRE TYPE

Network Wiring	One Unshielded Twisted Pair
	24-16 AWG (0.5-1.31mm)
Category Type	2 or better
Impedance	100 ± 20 ohms
DC Loop Resistance	52 ohms per 1,000ft (18 ohms per 100m)
Differential Capacitance	19 pF/ft max (62 pF/m max)

MECHANICAL


Dimensions, excluding brackets and connectors	3.00 x 1.54 x 1.10in (76 x 39 x 28mm)
Packaged weight	4.0oz (100g)
Material	Black ABS
Mounting	Two 0.175in (4.4mm) diameter holes 2.5in (63.5mm) apart
Product weight	4.0oz (100g)
Packaged weight	4.0oz (100g)

Up to ten NV-213A's can be mounted to an NV-RM 8/10 Rackmount Panel


Specifications subject to change without notice.

Typical Applications

Passive to Passive Application up to 750ft (225m)



Passive to Active Application up to 3,000ft (1km)



Network Video Technologies

4005 Bohannon Drive • Menlo Park, CA 94025 • USA
 (+1) 650.462.8100 • FAX (+1) 650.326.1940
 nvt.com • www.nvt.com/email

Copyright © 2011 NVT, Inc.
 410-213-1-N