



PANDUIT* PART NO.	BUNDLE DIA.		A	B	C	D	E	F	G	H	MAX PANEL THICKNESS in (mm)	MIN. LOOP TENSILE lbs (N)	CROSS SECTION	WEIGHT 100 pcs lbs (g)
	MAX. in (mm)	MIN. in (mm)												
PLP1.51	.06 (1.5)	1.25 (31.8)	.045 (1.1)	.135 (3.4)	.350 (8.9)	.236 (6.0)	.270 (6.9)	6.13 (156)	.260 (6.6)	.187 (4.7)	.093 (2.4)	40 (178)	INTERMEDIATE	.17 (77)

NOTE:

- *1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
- 2) THESE PARTS ARE RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.
- 3) SEE DRAWING SS-26803(A) FOR PLP1S, PLP1.5S & PLP2S.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

STRAP, PUSH MOUNT - PLP

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .1(2.5) (.XXX) ± .020 (.51)
(.XX) ± .02(.5) ANGLES ± -----

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
RAM
DATE
2-1-94
CHK'D
HVP

MAT'L:
NYLON 6.6

SCALE
DRAWING NO.
SS-26888
DWG
A
SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
---	----	---		REVISED HEAD ON TIE, DOES NOT HAVE THE LEDGE ON TOP VIEW OF HEAD	----	---		
3	1/29/04	JABO		CHANGED FORMAT FOR CONSISTENCY SEE ECN FOR DETAILS	26888	3		