

SMT-1723/1722

17" TFT-LCD Monitor




Key Features

- Supports up to 1280 x 1024 resolution
- High contrast ratio 1000 : 1
- Fast response time 5ms
- 120Hz motion technology
- Adjustable height

Dimensions

Unit : mm (inch)



Technical Specifications

SMT-1723/1722		
DISPLAY		
Screen Size		17"
Max. Resolution		1,280 x 1,024
Brightness		250cd/m ²
Contrast Ratio		1,000 : 1
Aspect Ratio		4 : 3
Viewing Angle (H/V)		170° / 160°
Display Color		16.7million
Response Time		5ms
Video System		NTSC / PAL
Panel Life		50,000hours
Filter Type		3D combfilter
INTERFACE		
Video	Connector	BNC types (2 in / 2 out)
S-Video	Connector	1CH input (Y/C), Loop through out
	Connector	1 Analog RGB 15-pin D-sub
RGB / DVI	Input Signal	0.7 Vp-p ±5%
	Available Format	720 x 400@70Hz
		640 x 480@60Hz/72Hz/75Hz (VGA)
		800 x 600@56Hz/60Hz/72Hz/75Hz (SVGA)
		1,024 x 768@60Hz/70Hz/75Hz (XGA)
		1,152 x 864@75Hz
		1,280 x 720@60Hz
Audio	Connector	2 RCA type (2 Stereo inputs)
	Output Signal	Speakers : 2 x 1W
	Application Support	
	Remote controller	
ON SCREEN DISPLAY		
Functions		Motion technology (120Hz), VESA™ DPM compatible, PIP/PBP
Language		English, Spanish, French, German, Italian, Portuguese, Dutch, Russian, Swedish, Chinese, Japanese, Korean
GENERAL		
Electrical	Input Voltage	SMT-1723 : 12V DC (External power supply) SMT-1722 : 100 ~ 240V AC (50/60Hz)
	Power Consumption	Type 23W
Environmental	Operating Temperature	0 ~ +40°C (+32°F ~ +104°F)
	Operating Humidity	20% ~ 90% (Non-condensing)
Mechanical	Dimensions with Stand (WxHxD)	371.0 x 368.0 x 220.0mm (14.61" x 14.49" x 8.66")
	Dimensions without Stand (WxHxD)	371.0 x 331.0 x 67.0mm (14.61" x 13.03" x 2.64")
	Weight	5.95Kg (13.12 lb)
	LCD Protection Glass	Yes
	Cabinet Color	Black
	VESA Mounts Interface	100 x 100mm