

# OLFLEX® FD VFD

Continuous Flex VFD Cable with UL & CSA TC Approval



OLFLEX® FD VFD is a continuous flex shielded motor cable for VFD Drives. It is designed with “Lapp Surge Guard” semi-conductive material to hold up to nonlinear power distortions associated with VFD drives and has an elastomeric alloy jacket for industrial applications.

### Recommended Applications:

VFD drive and motor connections in continuous flex applications, Machine tool, Plastic extrusion, any on/off applications using a VFD drive and motor










### Application Advantage:

- Continuous Flex rated for cable track applications
- “Lapp Surge Guard” protection to eliminate cable failure due to electrical disturbances
- Industrial Grade & Chemical Resistant elastomeric alloy jacket passing Oil Res I & II
- Corona Inception Voltage is 2900 volts
- Double shielded for extra protection
- UL TC-ER & CSA TC approved







### OLFLEX® FD VFD Construction:

Finely stranded bare copper conductors; specially formulated “Lapp Surge Guard” insulation; dry lubricant, barrier tape; 100% shielding with foil tape and tinned copper braid (70% coverage); specially formulated TPE black jacket.

OLFLEX® FD VFD (UL) TYPE TC-ER 90°C 600V c(UL) CIC/TC FT4 CSA AWM CE

<b>Cable Attributes, See Page 653</b>  Oil Resistance: OR-03  Flame Resistance: FR-03  Motion Type: CF-01  Mechanical Properties: MP-03		<b>Availability:</b>  Standard put-ups are 100ft, 250ft, 500ft, and 1,000ft. Bulk reels can be cut to length.	<b>Complete the installation with:</b>  VFD Selection Guide: Page 685  SKINTOP® Strain Relief: Page 486  EPIC® Connectors: Page 251  OLFLEX® Tubing: Page 546
---	--	--	---

### Technical Data:

 Minimum Bending Radius - for flexible use: 5 x cable diameter - for continuous flexing: 7.5 x cable diameter	 Color Code: Three black conductors with white numbers, plus green/yellow ground
 Temperature Range: -25°C to +105°C	 Approvals: <ul style="list-style-type: none"> <li>UL: - Type TC-ER, 90°C, - UL DP-1 90°C, UL-AWM 105°C, - UL Type MTW, NFPA 79 2007 - Oil Res I/II, Wet Rating 75°C - Class 1 Div. 2 per NEC Art. 336, 392, 501</li> <li>CSA: - c(UL) CIC/TC FT4 - AWM I/II A/B FT4</li> <li>Additional: - ICEA: T-24-380, Corona Test</li> </ul>
 Nominal Voltage: 600V- TC (UL & CSA) 1000V- TC Wind Turbine (WTTC)	
 Conductor Stranding: Very Fine Wire, Class 6	

Part Number	Number of Conductors includes ground	Nominal Outer Diameter inches	mm	Copper Weight lbs/mft	Approx. Weight lbs/mft	kg/km	SKINTOP® MS-SCL (PG) Page 504	SKINTOP® MS-SC-M Brush (Metric) Page 506
14 AWG (105/34) 2.11 mm <sup>2</sup> 771404	4	.500	12.7	78	133	198	53112340	53112676
12 AWG (168/34) 3.38 mm <sup>2</sup> 771204	4	.575	14.6	121	180	268	53112350	53112676
10 AWG (259/34) 5.32 mm <sup>2</sup> 771004	4	.690	17.5	173	271	403	53112350	53112677

\* Additional sizes available upon request. Minimums may apply.