

SNB-7000

3Megapixel Full HD Network Camera



Lens not included



Key Features


- Max. 3M (2048 x 1536) resolution
- 16 : 9 Full HD (1080p) resolution support
- H.264, MJPEG dual codec
- WDR (supported in 2M mode only)
- Smart codec (ROI encoding)

Available Lenses / Accessories (optional):



Dimensions

Unit : mm (inch)



Technical Specifications

	SNB-7000N/P
VIDEO	
Imaging Device	1/2.8" 3M PS CMOS
Total Pixels	2,144(H) x 1,588(V)
Effective Pixels	2,096(H) x 1,561(V)
Scanning System	Progressive
Min. Illumination (TBD)	Color : 1Lux (F1.2, 50IRE), 0.017Lux (Sens-up 60x) B/W : 0.08Lux (F1.2, 50IRE), 0.001Lux (Sens-up 60x)
S / N Ratio	50dB
Video Output	CVBS : 1.0Vp-p / 75Ω composite, 704 x 480(N), 704 x 576(P), for installation
LENS	
Lens Type	Manual / DC auto iris
Mount Type	C / CS
OPERATIONAL	
Camera Title	Off / On (Displayed up to 15 characters)
Day & Night	Auto (ICR) / Color / B/W / External B/W
Backlight Compensation	Off / BLC / HLC / WDR
Wide Dynamic Range	(*2M mode only), 52dB
Contrast Enhancement	SSDR (Samsung Super Dynamic Range) (Off / On)
Digital Noise Reduction	SSNR III (2D+3D noise filter) (Off / On)
Motion Detection	Off / On (4 programmable zones)
Privacy Masking	Off / On (1ea 4 point polygonal + 16ea rectangular zones)
Sens-up (Frame Integration)	Off / Auto (2x ~ 60x)
Gain Control	Off / Low / Medium / High
White Balance	ATW / AWC / Manual / Indoor / Outdoor
Electronic Shutter Speed	Auto / A.FLK / Manual (1/30 ~ 30,000sec)
Flip / Mirror	Off / On
Alarm I/O	Input 1ea / Output 1ea (Relay)
Remote Control Interface	RS-485
RS-485 Protocol	Samsung-T/E, Pelco-P/D, Sungjin
NETWORK	
Ethernet	RJ-45 (10/100BASE-T)
Video Compression Format	H.264, MJPEG
Resolution	3M mode - H.264 : Max. 20fps at all resolutions MJPEG : 800 x 600 ~ 320 x 180 - 20fps 1280 x 1024 ~ 1600 x 1200 - 15fps 1920 x 1080 ~ 2048 x 1536 - 10fps
	2M mode - H.264 : Max. 30fps at all resolutions (When WDR on, Max. framerate is Max. 15fps.) MJPEG : 800 x 600 ~ 320 x 180 - 30fps 1280 x 1024 ~ 1920 x 1080 : 15fps
	Max. Framerate
	3M mode : Max. 20fps, 2M mode : Max. 30fps * When WDR on, Max. framerate is Max. 15fps
Smart Codec	Yes (Area based method, Face detection method)
Video Quality Adjustment	H.264 : Compression level, Target bitrate level control MJPEG : Quality level control
Bitrate Control Method	H.264 : CBR or VBR, MJPEG : VBR
Streaming Capability	Multiple streaming (Up to 6 profiles)
Audio I/O	Mic / Line in, Line out
Audio Compression Format	G.711 u-law
Audio Communication	Bi-directional audio
IP	IPv4, IPv6
Protocol	TCP/IP, UDP/IP, RTP(UDP), RTP(TCP), RTSP, NTP, HTTP, HTTPS, SSL, DHCP, PPPoE FTP, SMTP, ICMP, IGMP, SNMPv1/v2c/v3(MIB-2), ARP, DNS, DDNS, ONVIF
Security	HTTPS(SSL) login authentication, Digest login authentication IP address filtering, User access log, 802.1x authentication
	Streaming Method
Max. User Access	Unicast / Multicast 10 users at unicast mode
Memory Slot	SD/SDHC memory slot
ONVIF Conformance	Yes
Webpage Language	English, French, German, Spanish, Italian, Chinese, Korean, Russian, Japanese, Swedish, Danish, Portuguese, Turkish, Polish, Czech, Rumanian, Serbian, Dutch, Croatian, Hungarian, Greek
Web Viewer	Supported OS : Windows XP / VISTA / 7, MAC OS
	Supported Browser : Internet Explorer 7.0 or Higher, Firefox, Google Chrome, Apple Safari
Central Management Software	NET-i viewer
ENVIRONMENTAL	
Operating Temperature / Humidity	-10°C ~ +50°C (+14°F ~ +122°F) / 20% ~ 80% RH
ELECTRICAL	
Input Voltage	12V DC, 24V AC, PoE (IEEE802.3af)
Power Consumption	Max. 7W
MECHANICAL	
Color / Material	Dark gray / Metal
Dimensions (WxHxD)	72.0 x 60.0 x 136.8mm (2.83" x 2.36" x 5.39")
Weight	440g (0.97 lb)