

CVC648IRHQ	3.6mm lens, black housing
CVC648IRHQW	3.6mm lens, white housing
CVC648IRVFHQ	2.8 - 12mm auto iris varifocal lens, black housing
CVC648IRVFHQW	2.8 - 12mm auto iris varifocal lens, white housing

Features

- Color day & night camera with special shielding to eliminate IR reflections
- 600 lines resolution
- Used for indoor applications
- Covers a full spectrum of possible lighting situations; ranging from bright light to no light
- This dome camera can be wall or ceiling mounted with the included mounting bracket
- IR cut filter
- 5 year warranty



Specifications

Image Sensor	1/3" Sony Super HAD II™ CCD
Resolution.....	600 TV lines
Minimum Illumination.....	0 lux with IR on, 0.1 lux with IR off
Effective Pixels	768 (H) x 494 (V)
Iris.....	Electronic iris
	DC auto iris (varifocal version only)
Electronic Shutter Speed.....	1/60 sec. - 1/100,000 sec.
Effective IR Range.....	65' (depending on scene reflection)
Number of IR LED	22
LED IR Wave Length.....	850nm
S/N Ratio	More than 52dB (AGC off)
Gamma.....	0.45 typ.
Scanning System.....	2:1 interlace

Synchronization	Internal
Backlight Compensation.....	BLC / HLC
AGC.....	Yes
TV System.....	NTSC
Power Consumption	370mA
Power Supply	12VDC regulated
	(power supply included)
Housing	High impact ABS
Operating Temperature.....	14° F - 122° F
Storage Temperature.....	- 4° F - 140° F
Dimensions.....	3" (H) x 5" (Dia.)
Weight	14.1 oz.
Included in Package	Wall mount bracket

Speco Technologies is constantly developing and improving products.

We reserve the right to modify product design and specifications without notice and without incurring any obligation.

Rev. 1/25/12

For more information contact Speco Technologies

200 New Highway, Amityville, NY 11701 • Toll Free: 1-800-645-5516 • Fax: 631-957-9142 or 631-957-3880
www.specotech.com