




- | | | | | | |
|------------------------|-------------|------------------------|-------------|-----------------------|-------------|
| | | 44±0.500 [144.36±1.64] | 4-1499515-4 | 22±0.100 [72.18±0.33] | 2-1499515-2 |
| | | 43±0.500 [141.08±1.64] | 4-1499515-3 | 21±0.100 [68.90±0.33] | 2-1499515-1 |
| | | 42±0.500 [137.80±1.64] | 4-1499515-2 | 20±0.100 [65.62±0.33] | 2-1499515-0 |
| | | 41±0.500 [134.52±1.64] | 4-1499515-1 | 19±0.100 [62.34±0.33] | 1-1499515-9 |
| | | 40±0.500 [131.24±1.64] | 4-1499515-0 | 18±0.100 [59.06±0.33] | 1-1499515-8 |
| | | 39±0.400 [127.96±1.31] | 3-1499515-9 | 17±0.100 [55.78±0.33] | 1-1499515-7 |
| | | 38±0.400 [124.68±1.31] | 3-1499515-8 | 16±0.100 [52.50±0.33] | 1-1499515-6 |
| | | 37±0.400 [121.40±1.31] | 3-1499515-7 | 15±0.100 [49.22±0.33] | 1-1499515-5 |
| | | 36±0.400 [118.12±1.31] | 3-1499515-6 | 14±0.100 [45.93±0.33] | 1-1499515-4 |
| 90±1.000 [295.29±3.28] | 9-1499515-0 | 35±0.400 [114.84±1.31] | 3-1499515-5 | 13±0.100 [42.65±0.33] | 1-1499515-3 |
| 80±1.000 [262.48±3.28] | 8-1499515-0 | 34±0.300 [111.55±0.98] | 3-1499515-4 | 12±0.075 [39.37±0.25] | 1-1499515-2 |
| 75±1.000 [246.08±3.28] | 7-1499515-5 | 33±0.300 [108.27±0.98] | 3-1499515-3 | 11±0.075 [36.09±0.25] | 1-1499515-1 |
| 70±1.000 [229.67±3.28] | 7-1499515-0 | 32±0.300 [104.99±0.98] | 3-1499515-2 | 10±0.075 [32.81±0.25] | 1-1499515-0 |
| 60±0.500 [196.86±1.64] | 6-1499515-0 | 31±0.300 [101.71±0.98] | 3-1499515-1 | 9±0.075 [29.53±0.25] | 1499515-9 |
| 55±0.500 [180.46±1.64] | 5-1499515-5 | 30±0.300 [98.43±0.98] | 3-1499515-0 | 8±0.075 [26.25±0.25] | 1499515-8 |
| 51±0.500 [167.33±1.64] | 5-1499515-1 | 29±0.200 [95.15±0.66] | 2-1499515-9 | 7±0.075 [22.97±0.25] | 1499515-7 |
| 50±0.500 [164.05±1.64] | 5-1499515-0 | 28±0.200 [91.87±0.66] | 2-1499515-8 | 6±0.075 [19.69±0.25] | 1499515-6 |
| 49±0.500 [160.77±1.64] | 4-1499515-9 | 27±0.200 [88.59±0.66] | 2-1499515-7 | 5±0.075 [16.41±0.25] | 1499515-5 |
| 48±0.500 [157.49±1.64] | 4-1499515-8 | 26±0.200 [85.31±0.66] | 2-1499515-6 | 4±0.075 [13.12±0.25] | 1499515-4 |
| 47±0.500 [154.21±1.64] | 4-1499515-7 | 25±0.200 [82.03±0.66] | 2-1499515-5 | 3±0.050 [9.84±0.16] | 1499515-3 |
| 46±0.500 [150.93±1.64] | 4-1499515-6 | 24±0.100 [78.74±0.33] | 2-1499515-4 | 2±0.050 [6.56±0.16] | 1499515-2 |
| 45±0.500 [147.65±1.64] | 4-1499515-5 | 23±0.100 [75.46±0.33] | 2-1499515-3 | 1±0.040 [3.28±0.13] | 1499515-1 |
| L — METERS [FEET] | PART NO | L — METERS [FEET] | PART NO | L — METERS [FEET] | PART NO |

THIS DRAWING IS A CONTROLLED DOCUMENT.						DWN:	L HALL	01MAR2005				TE Connectivity		
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK:	C CASH	APVD:	C CASH	04MAR2005	NAME CABLE ASSY, MRJ 21/MRJ 21 CAT 5e, GRAY, CMR					
		0 PLC ± -		PRODUCT SPEC		- -								
		1 PLC ± -		108-2235										
		2 PLC ± -		APPLICATION SPEC										
MATERIAL -		ANGLES FINISH ± -		WEIGHT -		SIZE A1		CADE CODE 00779		DRAWING NO C=1499515		RESTRICTED TO -		
CUSTOMER DRAWING						SCALE		NTS		SHEET		1 OF 2 REV F1		

