


Restricted to: General Release

USED ON

1907380 THIS DRAWING IS A CONTROLLED DOCUMENT



Left Side
 Connector(s): SC-Duplex
 Mode: MM
 Housing Color: Beige
 Geom. Spec: N/A

Fiber Path

A - _____ - B
 B - _____ - A

Right Side
 Connector(s): LC-Duplex
 Mode: MM
 Housing Color: Beige
 Geom. Spec: N/A

- Notes:
- 1 Includes dust caps (not shown on print).
 - 2 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
 - 3 IL tested at 1300nm.
 - 4 Label 2 will not be present on any cable assembly less than 5 meters long.

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS TO BE KEPT CONFIDENTIAL AND NOT DISCLOSED TO ANY OTHER PERSONS OR ORGANIZATIONS WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA

LOC
 CE
 DIST
 16

A	Rev Per	EC#	RELEASE	9/26/2006	-	MK	
P	LTR	REVISION RECORD		DATE	DIN	APVD	

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
meters	0 PLC ± .
	1 PLC ± .
	2 PLC ± .
	3 PLC ± .
	4 PLC ± .

DIN	Cable Assy Configurator	MATERIAL	HEAT TREAT
CHK	Michael Kepko		
APVD	Michael Kepko	Tyco Electronics, Inc. Harrisburg, PA 17105-3608	
NAME	FO C/A - 2 fiber, 50/125, OFNR (Riser) jacket, SC-Duplex to LC-Duplex		
SCALE	SIZE	DRAWING NO	SHEET
NTS	A2	C- 1907380	1 of 3
			REV
			A

Customer Print

Restricted to: General Release

USED ON

THIS DRAWING IS A CONTROLLED DOCUMENT.

Part #	L (meters)	L (feet)	SC-Duplex, Beige		LC-Duplex, Beige	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
0-1907380-1	0.950 - 1.050	3.11 - 3.44	0.5	-	0.5	-
0-1907380-2	1.950 - 2.050	6.39 - 6.72	0.5	-	0.5	-
0-1907380-3	2.950 - 3.050	9.67 - 10.00	0.5	-	0.5	-
0-1907380-4	3.920 - 4.080	12.86 - 13.38	0.51	-	0.51	-
0-1907380-5	4.920 - 5.080	16.14 - 16.66	0.51	-	0.51	-
0-1907380-6	5.920 - 6.080	19.42 - 19.94	0.51	-	0.51	-
0-1907380-7	6.920 - 7.080	22.70 - 23.22	0.51	-	0.51	-
0-1907380-8	7.920 - 8.080	25.98 - 26.50	0.51	-	0.51	-
0-1907380-9	8.850 - 9.150	29.03 - 30.01	0.51	-	0.51	-
1-1907380-0	9.850 - 10.150	32.31 - 33.30	0.52	-	0.52	-
1-1907380-1	10.850 - 11.150	35.59 - 36.58	0.52	-	0.52	-
1-1907380-2	11.850 - 12.150	38.87 - 39.86	0.52	-	0.52	-
1-1907380-3	12.850 - 13.150	42.15 - 43.14	0.52	-	0.52	-
1-1907380-4	13.850 - 14.150	45.43 - 46.42	0.52	-	0.52	-
1-1907380-5	14.850 - 15.150	48.72 - 49.70	0.52	-	0.52	-
1-1907380-6	15.840 - 16.160	51.96 - 53.01	0.52	-	0.52	-
1-1907380-7	16.830 - 17.170	55.21 - 56.33	0.53	-	0.53	-
1-1907380-8	17.820 - 18.180	58.46 - 59.64	0.53	-	0.53	-
1-1907380-9	18.810 - 19.190	61.71 - 62.95	0.53	-	0.53	-
2-1907380-0	19.800 - 20.200	64.96 - 66.27	0.53	-	0.53	-
2-1907380-1	20.790 - 21.210	68.20 - 69.58	0.53	-	0.53	-
2-1907380-2	21.780 - 22.220	71.45 - 72.90	0.53	-	0.53	-
2-1907380-3	22.770 - 23.230	74.70 - 76.21	0.53	-	0.53	-
2-1907380-4	23.760 - 24.240	77.95 - 79.52	0.54	-	0.54	-
2-1907380-5	24.750 - 25.250	81.20 - 82.84	0.54	-	0.54	-
2-1907380-6	25.740 - 26.260	84.44 - 86.15	0.54	-	0.54	-
2-1907380-7	26.730 - 27.270	87.69 - 89.46	0.54	-	0.54	-
2-1907380-8	27.720 - 28.280	90.94 - 92.78	0.54	-	0.54	-
2-1907380-9	28.710 - 29.290	94.19 - 96.09	0.54	-	0.54	-
3-1907380-0	29.700 - 30.300	97.44 - 99.40	0.55	-	0.55	-
3-1907380-1	30.690 - 31.310	100.68 - 102.72	0.55	-	0.55	-
3-1907380-2	31.680 - 32.320	103.93 - 106.03	0.55	-	0.55	-
3-1907380-3	32.670 - 33.330	107.18 - 109.35	0.55	-	0.55	-
3-1907380-4	33.660 - 34.340	110.43 - 112.66	0.55	-	0.55	-
3-1907380-5	34.650 - 35.350	113.68 - 115.97	0.55	-	0.55	-
3-1907380-6	35.640 - 36.360	116.92 - 119.29	0.55	-	0.55	-
3-1907380-7	36.630 - 37.370	120.17 - 122.60	0.56	-	0.56	-
3-1907380-8	37.620 - 38.380	123.42 - 125.91	0.56	-	0.56	-
3-1907380-9	38.610 - 39.390	126.67 - 129.23	0.56	-	0.56	-
4-1907380-0	39.600 - 40.400	129.92 - 132.54	0.56	-	0.56	-
5-1907380-0	49.500 - 50.500	162.40 - 165.68	0.58	-	0.58	-

Qty	U of M	Description	Item No.
4	piece	LC, SC, FC Straight Boot, Beige	1
1	piece	LC Duplex clip, black	2
2	piece	LC Connector Assy, MM	3
2	piece	SC Simplex Housing, Beige	4
2	piece	2.5mm ferrule cover	5
AR	meter	2 fiber, 50/125, 2.0mm, Twinzip, Orange, OFNR (Riser)	6
2	piece	SC Duplex Clip	7
4	piece	Eyelet/Shrink tube assembly - White	8
2	piece	CONN SUBASSY, MM, SC 1.6MM	9
2	piece	Trace Label	10

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION AND IS NOT TO BE DISCLOSED TO ANY OTHER PARTY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16

Rev Per	EC#	RELEASE	9/26/2006	-	MK
P	LTR	REVISION RECORD	DATE	DN	APVD

Customer Print

Customer Print

DIN Cable Assy Configurator		MATERIAL	HEAT TREAT
DIN Michael Kepko			
APVD Michael Kepko		AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608	
NAME FO C/A - 2 fiber, 50/125, OFNR (Riser) jacket, SC-Duplex to LC-Duplex			
SCALE NTS	SIZE A2	DRAWING NO C- 1907380	SHEET 2 of 3
REV A			

8 7 6 5 4 3 2 1

Restricted to: General Release

USED ON

THIS DRAWING IS A CONTROLLED DOCUMENT.

Label 1

Per specification 107-1645-1



- Trace # - Bar Code
- Trace # - Human Readable
- Part Number
- Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1



- Trace # - Bar Code
- Trace # - Human Readable
- Part Number
- Country of Origin

This label is used on all lengths on this drawing.

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION AND IS NOT TO BE DISCLOSED TO ANYONE OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
 CE
 DIST
 16

A	Rev Per EC#	RELEASE	9/26/2006	-	MK		
P	LTR	REVISION RECORD	DATE	DIN	APVD		

DIMENSIONS: meters	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± .
	1 PLC ± .
	2 PLC ± .
	3 PLC ± .
	4 PLC ± .

Customer Print

DIN	Cable Assy Configurator	MATERIAL	HEAT TREAT
OK	Michael Kepko		
APVD	Michael Kepko	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608	
NAME	FO C/A - 2 fiber, 50/125, OFNR (Riser) jacket, SC-Duplex to LC-Duplex		
SCALE	SIZE	DRAWING NO	SHEET
NTS	A2	C- 1907380	3 of 3
			REV
			A