


A	[.34]	[.043]	--	12	6.35	[.250]	UNPL	18	0.15	[.006]	03142	5-192038-0	OBSOLETE	16
A	[.34]	[.030]	--	12	6.35	[.250]	3-2	18	0.15	[.006]	03028	4-192038-9		
A	[.34]	[.030]	--	12	6.35	[.250]	1-2	18	0.15	[.006]	03086	4-192038-8		
A	[.34]	[.030]	--	12	6.35	[.250]	UNPL	18	0.15	[.006]	03074	4-192038-7	OBSOLETE	16
A	--	--	--	12	6.30	[.248]	UNPL	19	0.30	[.012]	--	4-192038-6	15	
A	--	--	--	12	6.30	[.248]	UNPL	19	0.28	[.011]	--	4-192038-5	15	
A	[.35]	[.034]	--	12	6.30	[.248]	3-2	19	0.25	[.010]	03025	4-192038-4		16
A	[.35]	[.034]	--	12	6.30	[.248]	1-2	19	0.25	[.010]	03147	4-192038-3	OBSOLETE	
A	[.35]	[.034]	--	12	6.30	[.248]	UNPL	19	0.25	[.010]	03111	4-192038-2		
A	[.32]	[.038]	--	12	6.00	[.236]	4-2	17	0.20	[.008]	03137	4-192038-1		
A	[.32]	[.038]	--	12	6.00	[.236]	3-2	17	0.20	[.008]	03023	4-192038-0		
A	[.32]	[.038]	--	12	6.00	[.236]	1-2	17	0.20	[.008]	03065	3-192038-9		16
A	[.32]	[.034]	--	12	6.00	[.236]	UNPL	17	0.20	[.008]	03061	3-192038-8	OBSOLETE	
A	[.33]	[.034]	--	12	6.00	[.236]	3-2	17	0.15	[.006]	03022	3-192038-7		
A	[.33]	[.034]	--	12	6.00	[.236]	1-2	17	0.15	[.006]	03113	3-192038-6		16
A	[.33]	[.034]	--	12	6.00	[.236]	UNPL	17	0.15	[.006]	03021	3-192038-5	OBSOLETE	
NOT AVAILABLE												3-192038-4	15	
A	[.35]	[.020]	--	13	6.00	[.236]	--	17	0.12	[.005]	03085	3-192038-3		16
												3-192038-2		16
A	[.26]	[.034]	--	12	5.00	[.197]	3-2	15	0.20	[.008]	03019	3-192038-1	OBSOLETE	
A	[.26]	[.034]	--	12	5.00	[.197]	1-2	15	0.20	[.008]	03131	3-192038-0		
A	[.26]	[.034]	--	12	5.00	[.197]	UNPL	15	0.20	[.008]	03130	2-192038-9		
A	[.26]	[.031]	--	12	5.00	[.197]	3-2	15	0.15	[.006]	03018	2-192038-8		
A	[.26]	[.031]	--	12	5.00	[.197]	1-2	15	0.15	[.006]	03064	2-192038-7		16
A	[.26]	[.031]	--	12	5.00	[.197]	5	15	0.15	[.006]	03103	2-192038-6	OBSOLETE	
A	[.26]	[.031]	--	12	5.00	[.197]	UNPL	15	0.15	[.006]	03060	2-192038-5	OBSOLETE	
A	[.23]	[.034]	--	12	4.00	[.157]	3-2	14	0.20	[.008]	03013	2-192038-4		
A	[.23]	[.030]	--	12	4.00	[.157]	3-2	14	0.15	[.006]	03012	2-192038-3		16
A	[.21]	[.030]	--	12	3.50	[.138]	3-2	13	0.15	[.006]	03011	2-192038-2		
A	[.21]	[.034]	--	12	3.17	[.125]	3-2	12	0.20	[.008]	03010	2-192038-1	OBSOLETE	
A	[.21]	[.034]	--	12	3.17	[.125]	1-2	12	0.10	[.004]	03132	2-192038-0		
A	[.21]	[.034]	--	12	3.17	[.125]	5	12	0.10	[.004]	03133	1-192038-9		
A	[.21]	[.034]	--	12	3.17	[.125]	UNPL	12	0.10	[.004]	03134	1-192038-8		
A	[.20]	[.030]	--	12	3.00	[.118]	3-2	11	0.15	[.006]	03009	1-192038-7		
A	[.19]	[.030]	--	12	3.00	[.118]	3-2	10	0.15	[.006]	03008	1-192038-6		
A	[.18]	[.030]	--	12	2.67	[.105]	3-2	9	0.15	[.006]	03007	1-192038-5		
A	[.18]	[.030]	--	12	2.31	[.091]	3-2	8	0.15	[.006]	03006	1-192038-4		16
A	[.15]	[.030]	--	12	2.03	[.080]	3-2	7	0.15	[.006]	03005	1-192038-3		
A	[.15]	[.030]	--	12	1.70	[.067]	3-2	6	0.15	[.006]	03004	1-192038-2		
C	--	[.038]	NOTE 14	12		--	3-2	--	0.20	[.008]	03000	1-192038-1	OBSOLETE	
C	--	[.038]	NOTE 14	12		--	1-2	--	0.20	[.008]	03095	1-192038-0		
C	--	[.038]	NOTE 14	12		--	UNPL	--	0.20	[.008]	03077	192038-9		
C	--	[.034]	NOTE 14	12		--	4-2	--	0.15	[.006]	03123	192038-8		
C	--	[.034]	NOTE 14	12		--	3-2	--	0.15	[.006]	03053	192038-7	OBSOLETE	
C	--	[.034]	NOTE 14	12		--	1-2	--	0.15	[.006]	03104	192038-6		
C	--	[.034]	NOTE 14	12		--	UNPL	--	0.15	[.006]	03001	192038-5		16
NOT AVAILABLE												192038-4		
NOT AVAILABLE												192038-3	OBSOLETE	
NOT AVAILABLE												192038-2		
NOT AVAILABLE												192038-1		
STYLE	FREE DIA	LH	LENGTH	MAT'L (NOTE)	MATING PIN Ø REF	PLATING NOTE NO.	NUM LOUV	MAT'L THK	REF	PART NO.				



1. FINISH—SILVER PLATE 200 μIN MIN THICK.
2. FINISH—NICKEL PLATE 40 μIN MIN THICK.
3. FINISH—GOLD PLATE 10 μIN MIN THICK.
4. FINISH—GOLD PLATE 50 μIN MIN THICK.
5. FINISH—NICKEL PLATE 80 μIN MIN THICK.
6. FINISH—TIN PLATE 300 μIN MIN THICK.
7. NOT USED.
8. NOT USED.
9. NOT USED.
10. NOT USED.
11. PLATING NOTE ARE TO BE INTERPRETED AS FOLLOWS, 6-8 AS 6 OVER 8.
12. MATERIAL—CDA172, BeCu.
13. MATERIAL—STAINLESS STEEL.
14. PRODUCT IS SOLD BY THE FOOT.
15. OBSOLETE PART NUMBER.
16. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RA JAYNE 08-13-91	TE Connectivity		
		CHK RA JAYNE 08-13-91			
DIMENSIONS: MM [INCHES]		APVD RA JAYNE 08-13-91	NAME CONTACT BAND,FEMALE		
		PRODUCT SPEC		SIZE CAGE CODE DRAWING NO	
		APPLICATION SPEC		RESTRICTED TO	
MATERIAL SEE TABLE		WEIGHT		A2 00779 C-192038	
CUSTOMER DRAWING			SCALE NTS	SHEET 1 of 2	REV H2

