

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
FT	8		AC1	REVISED PER ECO-06-5544	3/14/06	SS
			AC2	REVISED PER ECO-09-021826	11JAN10	KK



APVD	GS
APVD	AEG

D



- 1 AMP, PART NUMBER AND DATE CODE, INK STAMPED ON (1) OR BOTH SIDES.
- 2 HEXAVALENT CHROMATE COATING.
- 3 NON-HEXAVALENT CHROMATE COATING.
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI


C



B

4 OBSOLETE 4 OBSOLETE	3	11.05–13.84[.435–.545]	1	NICKEL PER QQ–N–290	CARBON STEEL	200517–9
	2	7.62–11.43[.300–.450]	1	NICKEL PER QQ–N–290	CARBON STEEL	200517–8
	2	11.05–13.84[.435–.545]	–	CLEAR ANODIZED	ALUMINUM ALLOY	200517–7
	2	11.05–13.84[.435–.545]	1	NICKEL PER QQ–N–290	CARBON STEEL	200517–2
	2	11.05–13.84[.435–.545]	1	CLEAR ANODIZED	ALUMINUM ALLOY	200517–1
	NOTES	CABLE RANGE DIA	MARKING	FINISH	MATERIAL	PART NUMBER

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.FOLTZ 01/23/95		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
		CHK R.STONE 01/24/95			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME SHIELD KIT, UNASSEMBLED, SHORT, 34 POSITION, M SERIES —	
		0 PLC ± —			
		1 PLC ± —			
		2 PLC ± 0.38 [.015]			
		3 PLC ± —			
		4 PLC ± —			
ANGLES ± —		APVD —		SIZE A2	
		PRODUCT SPEC —			
		APPLICATION SPEC —		DRAWING NO C=200517	
		—		RESTRICTED TO —	
MATERIAL SEE CALLOUTS		FINISH SEE CALLOUTS		WEIGHT —	
				CUSTOMER DRAWING	
				SCALE 2:1	
				SHEET 1 of 1	
				REV AC2	