

# IQeye Alliance-pro

## H.264 Megapixel IP Dome Camera

### Features

- > Resolutions up to 5 MP
- > H.264 Main profile + MJPEG Compression
- > 60 fps @ 720p, 30 fps @ 1080p, 10 fps @ 5 MP
- > Two-Way Audio
- > Day/Night Movable IR Filter
- > Lightgrabber™ II Low-light Feature
- > Power Over Ethernet, 12-24 VDC, 24 VAC
- > IP66/NEMA 4 Outdoor Enclosure
- > Indoor/Outdoor Vandal Resistant Dome
- > On-Camera Storage
- > Direct-to-Storage
- > 5 Year Warranty

The Alliance-pro is a full featured, multi-megapixel H.264 Main Profile vandal dome camera. With support for up to 5MP resolutions, this camera provides multiple, individually configured H.264 and simultaneous MJPEG streams. Designed with the installer in mind, installation and maintenance is easy thanks to the intuitive design, hinged pivoting shroud, 3-axis gimbal, EZglide lens focus, and analog output for focusing.

The Alliance-pro can be installed virtually anywhere using Power-over-Ethernet or AC or DC power and supports a movable IR filter for day and night operation as well as controls for optimizing video for any lighting condition. Two-way audio allows for interactive communication between the camera and monitoring site. The external on camera micro SDHC memory expansion port in combination with IQrecorder, or Direct-To-Storage recording, make the Alliance-pro a flexible stand-alone platform ideal for motion based recording or remote monitoring.



**IQ inVision** 

33122 Valle Road  
San Juan Capistrano, CA  
92675-4853  
USA

toll free within US 877.850.0805  
phone +1.949.369.8100  
fax +1.949.369.8105

[www.iqeye.com](http://www.iqeye.com)



### Specifications

#### Video

<b>Compression</b>	H.264 and MJPEG
<b>H.264 Profile</b>	Main
<b>Sensor</b>	1/3" CMOS, 1/2.5" CMOS for 5 MP
<b>JPEG Compression Quality Settings</b>	User Configurable
<b>Shutter Speed</b>	Auto/Programmable/Fixed
<b>Image Settings</b>	Saturation, Contrast, Brightness, Sharpness, Lightgrabber™ II
<b>Exposure</b>	User Configurable
<b>White Balance</b>	Auto/Programmable
<b>Backlight Compensation</b>	Auto
<b>IR Range</b>	800 to 940 nm

#### Features

<b>Virtual Cameras</b>	User Configurable Windows
<b>Image Crop</b>	User Configurable Windows
<b>Motion Detection</b>	User Configurable Windows
<b>Access Hours</b>	User Configurable
<b>Time Lapse Recording</b>	User Configurable
<b>Event Based Recording</b>	User Configurable
<b>Flip and Rotate</b>	90, Horizontal, Vertical
<b>Analog Service Port</b>	NTSC/PAL
<b>Audio Support</b>	Two-way G.711 PCM 8 kHz
<b>Analytics Ready</b>	Yes
<b>On-Camera IQapps</b>	IQaccess
<b>System Integration</b>	ONVIF, PSIA, IQfinder, IQsentry, IQmanager, Direct-to-Storage, IQrecorder, IQevent

#### Network

<b>Supported Protocols</b>	TCP/IP, HTTP, HTTPS, DHCP, UDP, RTP, RTSP, DNS, ARP, ICMP, NTP, UPnP, ZeroConf, APIPA, UDP multicast, SNMP, FTP, SMTP, Telnet, CIFS
<b>Password Protection</b>	Secure Multi-level

#### Input/Output

<b>Input Power</b>	Power over Ethernet 802.3af Class 1, Class 2 (NX) 24 VAC, 12-24 VDC
<b>Power Consumption</b>	< 3.4 W (typical) < 5.2W NX (typical)
<b>AC Lighting</b>	50 Hz/60 Hz Selectable
<b>Network Interface</b>	RJ45 10Base-T/100Base-TX
<b>Physical I/O</b>	1 input, 1 output
<b>Audio I/O</b>	Mic in/Line in, Line out
<b>On Camera Storage</b>	Micro SD Class 6+

#### Misc


<b>Ingress Protection Rating</b>	IP66, NEMA 4 (NE/NX)						
<b>Approvals</b>	FCC, CE						
<b>Temperature Range</b>	-4°F to 122°F, -20°C to 50°C -22°F to 122°F, -30°C to 50°C (NX)						
<b>Weight (grams)</b>	746 g (NI), 1186 g (NE), 1193 g (NX)						
<b>Warranty</b>	5 years						
<b>Lens Options</b>	B5 Wide Angle Lens 1/3" M14, 3-13 mm, F1.4, IR B6 Wide Angle Lens 1/2.5" M14, 3.3-12 mm, F1.4, IR						
<b>Accessories</b>	<table> <tr> <td>IQAE-BOX</td><td>Back Box</td></tr> <tr> <td>IQA-WM</td><td>Wall Mount Adaptor</td></tr> <tr> <td>IQ800-PMA</td><td>Pole Mount Adaptor</td></tr> </table>	IQAE-BOX	Back Box	IQA-WM	Wall Mount Adaptor	IQ800-PMA	Pole Mount Adaptor
IQAE-BOX	Back Box						
IQA-WM	Wall Mount Adaptor						
IQ800-PMA	Pole Mount Adaptor						

### Product Configurations

Part Number	Maximum Resolution	Maximum Frame Rate	Minimum Illumination
IQA30Nx-B5	SD480p - 720 x 480	30 fps	Color: 0.1 lux, B/W: <0.05 lux
IQA31Nx-B5	HD720p - 1280 x 720	60 fps	Color: 0.1 lux, B/W: <0.05 lux
IQA32Nx-B5	HD1080p - 1920 x 1080	30 fps	Color: 0.2 lux, B/W: <0.05 lux
IQA33Nx-B5	3.6 MP - 2560 x 1440 3.1 MP - 2048 x 1536	16 fps 20 fps	Color: 0.3 lux, B/W: <0.05 lux
IQA35Nx-B6	5 MP - 2560 x 1920	10 fps	Color: 0.3 lux, B/W: <0.05 lux

**I** - Internal/Indoor    **E** - External/Outdoor    **X** - Extreme Temperature Outdoor


### Dimensions



Top



Side (without back box)



Side (with backbox)