






LOC		DIST		REVISIONS				
F	LTR	DESCRIPTION			DATE	DWN	APVD	
	A	RLSD; ECO-09-027567			14DEC2009	GG	RA	


- ALL DIMENSIONS SHOWN ARE NOMINAL
UNLESS OTHERWISE SPECIFIED.
- MATERIAL:
SHIELDED CASE - COPPER C2680, T=0.25MM, 30u" NICKEL PLATED
COUPLER HOUSING - ABS HIGH-IMPACT UL94V-0 THERMOPLASTIC
SPRING WIRE - PHOSPHOR BRONZE 5100W TEMPER WIRE,
Ø=0.45MM, 50u" GOLD OVER 100u" NICKEL UNDERCOAT.
3. MOUNTING PANEL THICKNESS .062 [1.57] NOMINAL.



SCALE 4:1



SINGLE PANEL CUTOUT



SUGGESTED FLUSH MOUNT
PANEL APPLICATION CUTOUT

2111122-1				PART NUMBER			
DWN S. GARRETT 18NOV2009				Tyco Electronics Harrisburg, PA 17105-3608			
CHK R. ASHRY 18NOV2009				NAME COUPLER, SL, INLINE, CAT5E, SHIELDED			
APVD R. ASHRY 18NOV2009				SIZE CAGE CODE DRAWING NO A100779C-2111122			
PRODUCT SPEC				RESTRICTED TO			
APPLICATION SPEC				-			
WEIGHT				-			
CUSTOMER DRAWING				SCALE 6:1 SHEET 1 OF 1 REV A			