

- 1

DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- 2

MATERIAL:
CONNECTOR HOUSING - ABS MOLDING COMPOUND, NATURAL.
EDGE CONNECTOR HOUSING - POLYESTER MOLDING COMPOUND, BLACK.
STRAIN RELIEF - POLYCARBONATE MOLDING COMPOUND, LIGHT ALMOND, FLAME RETARDED.
EDGE CONNECTOR TERMINALS - PHOSPHOR BRONZE WITH 1.27µm[.000050] MINIMUM GOLD PLATE OVER 1.27µm[.000050] MINIMUM NICKEL PLATE IN CONTACT AREA, AND 3.05µm[.000120] MINIMUM MATTE TIN-LEAD IN WIRE TERMINATION AREA OVER 1.27µm[.000050] MINIMUM NICKEL UNDERPLATE OVER REST OF TERMINAL.
SCREWS - ZINC PLATED CARBON STEEL.
SHIELD CLIP - HIGH CARBON SPRING STEEL WITH 7.62µm[.000300] MINIMUM NICKEL ELECTROPLATE.
- 3

EDGE CONNECTOR SHOWN NOT ASSEMBLED BUT IS SHIPPED ASSEMBLED TO CONNECTOR HOUSING WITH NO.2 SELF TAPPING SCREW.
- 4



APPLICATION:

4.1 CONNECTOR HOUSING CAN SNAP INTO A 1.02-2.29[.040-.090] THICK PANEL BUT 1.52-2.29[.060-.090] IS RECOMMENDED.

4.2 TWO NO. 2 X 9.52[.375] LONG PAN HEAD SELF TAPPING SCREWS SUPPLIED WITH KIT MAY BE USED IN DIAGONAL LOCATIONS TO PROVIDE BEST FIT TO PANEL.

406360-1

PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING DEPARTMENT SHOULD BE CONTACTED FOR THE LATEST NOTATION.				DMN T. SPRINKLE 10DEC96		AMP AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: mm (INCHES)		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK T. SPRINKLE 10JAN97		NAME	
		0 PLC ±.0 1 PLC ±.0 2 PLC ±.0 3 PLC ±.0 4 PLC ±.0 ANGLES FINISH		APVD A. DUINN 10JAN97		WALLBOX KIT, SINGLE, UNSHIELDED, AMP COMMUNICATION OUTLET II	
MATERIAL		WEIGHT		SIZE		CAGE CODE	DRAWING NO
		-		A1		00779	C-406360
CUSTOMER DRAWING				SCALE		2:1 SHEET 1 OF 1 REV 0	