


THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , - .
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.		

PART NUMBER	FIBER TYPE 1.1 2.2	MAX ATTENUATION (dB/km)				MINIMUM OVERFILLED LAUNCH BANDWIDTH (MHz*km)		MINIMUM EFFECTIVE MODAL BANDWIDTH (MHz*km)	MINIMUM 10 GIGABIT ETHERNET LINK DISTANCE (meters)	A (mm)	JACKET COLOR 1.3	FLAME RATING 2.3	FIBER SPECIFICATION
		850nm	1300nm	1310nm	1550nm	850nm	1300nm	850nm	850nm				
1-1777117-7	62.5/125	3.5	1.2	N/A	N/A	200	500	N/A	33	13.3	ORANGE	OFCP	TIA-492AAAA-XBAXE
2-1777117-1	50/125	3.5	1.5	N/A	N/A	500	500	N/A	82	12.3	ORANGE INNER /BARE AL OUTER	OFCP	TIA-492AAAB-XBAX7
2-1777117-7	50/125	3.5	1.5	N/A	N/A	500	500	N/A	82	13.3	ORANGE	OFCP	TIA-492AAAB-XBAX7
3-1777117-6	50/125 OM3	3.2	1.2	N/A	N/A	1500	500	2000	300	15.8	AQUA	OFCR	TIA-492AAAC-XBAX
3-1777117-7	50/125 OM3	3.2	1.2	N/A	N/A	1500	500	2000	300	13.3	AQUA	OFCP	TIA-492AAAC-XBAX
7-1777117-7	50/125 OM4	3.2	1.2	N/A	N/A	3500	500	4700	550	13.3	AQUA	OFCP	TIA-492AAAD-XBAX
4-1777117-6	SINGLEMODE	N/A	N/A	0.5	0.5	N/A	N/A	N/A	N/A	15.8	YELLOW	OFCR	TIA-492CAAB-XBAXX ITU-T G.652.D
4-1777117-7	SINGLEMODE	N/A	N/A	0.5	0.5	N/A	N/A	N/A	N/A	13.3	YELLOW	OFCP	TIA-492CAAB-XBAXX ITU-T G.652.D

A triangle containing the number 2.2.A triangle containing the number 2.5.A triangle with the number 2.6 inside it.

LEGEND

A triangle with the number 2.1 inside it.

THIS DRAWING IS A CONTROLLED DOCUMENT.		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC	± -
	1 PLC	± -
	2 PLC	± -
	3 PLC	± -
	4 PLC	± -
ANGLES		± -
MATERIAL -		FINISH -

DWN	08JAN10	 Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608				
CHK	08JAN10					
APVD	08JAN10					
M. KEPKO						
PRODUCT SPEC		CABLE, ILJA, DISTRIBUTION, 12 FIBER —				
—						
APPLICATION SPEC						
—		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
WEIGHT —		A2	00779	G-1777117	—	
CUSTOMER DRAWING				SCALE	N.T.S.	SHEET 1 OF 1
				REV D		

1471-9 (1/08)

1777117

8

A