

LOC		DIST		REVISIONS			
AA	27	P	F	ZONE	LTR	DESCRIPTION	DATE
					M	REV; EC 0210-0840-94	3-2-95


- 1

DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- 2

MATERIAL: POLYESTER FILM 0.025 [0.010] THICK.
2 LAYERS EACH SIDE.
COPPER WIRE- 0.23 [0.009] THICK × 15.24 [0.600] WIDE.
SHIELD- PVC, 0.025 [0.010] THICK.
- 3

CABLE MARKED WITH "AMP INC PN 553239
TYPE FCC UL CSA 12 AWG, CU 300V, 20 AMP 60°C"
IN COLOR SPECIFIED FOR CONTINUOUS LENGTH OF ROLL AS SHOWN.
- 4

CAUTION: THE UNDERCARPET CABLE MAY NOT BE USED OUTDOORS OR IN WET LOCATIONS; WHERE THE CABLE WOULD BE SUBJECT TO CORROSIVE VAPORS; IN ANY HAZARDOUS (CLASSIFIED) LOCATION; OR IN RESIDENTIAL, SCHOOL, AND HOSPITAL BUILDINGS.



30.7	[101]	3-553239-4
15.5	[51]	3-553239-3
76.5	[251]	3-553239-1
LENGTH PER ROLL - M (FEET)		PART NO

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± -		DR 2-18-94 B. SIMPSON	AMP AMP Incorporated Harrisburg, PA 17105-3608		
MATERIAL		CHK - C. WHITT APPD - B. MCNEIL			
FINISH		APPD - D. MARGO PRODUCT SPEC 108-6038	NAME CABLE, FLAT, 5 CONDUCTOR, 12 AWG, POWER, UNDERCARPET		
WEIGHT		APPLICATION SPEC 114-6008	SIZE D	CAGE CODE 00779	DRAWING NO C-553239
			SCALE -		SHEET 1 OF 1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.