


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT By - ALL RIGHTS RESERVED.

FINISHED CABLE DATA		
CONDUCTORS	WIRE AWG	24 AWG SOLID
	MATERIAL	SOLID BARE COPPER ²
INSULATION	MATERIAL	POLYOLEFIN ²
JACKET	MATERIAL	FR PVC ²
FILLER	MATERIAL	POLYOLEFIN

COLOR CODE

PAIR	COLOR CODE
1	WHT-BLU/BLU
2	WHT-ORG/ORG
3	WHT-GRN/GRN
4	WHT-BRN/BRN



LOC	DIST	REVISIONS					
EH	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		V		REV ECO-12-012935	26JUL2012	GG	SS

- ¹ SEQUENTIAL FOOTAGE RETURNED TO ZERO FOR EACH LENGTH. ON PUTUP LENGTHS 3000 FT OR LESS.
- ² MATERIALS ARE SELECTED BASED ON THEIR ABILITY TO CONFORM TO UL 444 LATEST ISSUE.
- ³ XX = JACKET COLOR - BL = BLUE, WT = WHITE, GY = GRAY, GN = GREEN, YL = YELLOW, OR = ORANGE, RD = RED, VT = VIOLET, BK = BLACK.
- 4. PRINT COLOR SHALL BE DARK BLUE, EXCEPT WHITE ON BLACK JACKET.
- ⁵ DATE CODE.
- 6. GOVERNING SPECIFICATIONS - LATEST REVISIONS
 NEC 800
 UL444 CMR
 TIA 568-C.2 CAT 6
- ⁷ REPLACE "02" FOR THE FOLLOWING FOOTAGES:
 04=2000', 05=2500', CALL FOR ADDITIONAL OPTIONS.

CATALOG NUMBER	WEIGHT		PACKAGING
	LBS/KFT	KG/KM	
TE62DR-XX02	26	38	1,000' REEL
TE62DR-XXRB	27	40	1,000' REEL IN A BOX
TE62DR-XXII	25	37	1,000' REELEX

LEGEND TO BE REPEATED EVERY 24±.25'
 () TE CONNECTIVITY 620 SERIES 4/24 AWG T256 CMR C(UL)US ETL VERIFIED TIA-568-C.2 CAT 6 PAT 6153826 XXXX FT

¹ ⁵

³ ⁷

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	03AUG2001		TE TE Connectivity
DIMENSIONS: INCHES		CHK	09JUN00		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	09JUN00		
0 PLC ± 1 PLC ± .1 2 PLC ± .02 3 PLC ± .005 4 PLC ± .0005 ANGLES ±		PRODUCT SPEC	NAME		
MATERIAL	FINISH	APPLICATION SPEC		CABLE CATEGORY 6, 4UTP, 24 AWG, CMR	
		WEIGHT	SIZE	CAGE CODE	DRAWING NO
			A2	00779	C=219560
CUSTOMER DRAWING			SCALE	SHEET	REV
			NTS	1 of 1	V