


LOC	DIST	REVISIONS					
CE	16	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REVISED PER ECR-08-003592	12FEB08	JWD	JD

1. SEE TABLE FOR MAXIMUM CONNECTOR INSERTION LOSS AT 1300nm
2. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702



FIBER PATH DETAIL

0.95	0.65	300.0±3.00 [11811.0±118.0]	9-6374615-9
0.65	0.35	100.0±1.00 [3937.0±39.0]	9-6374615-8
0.59	0.29	60.00±0.60 [2362.0±24.0]	6-6374615-0
0.55	0.25	30.00±0.30 [1181.10±11.81]	3-6374615-0
0.53	0.23	25.0±0.30 [984.0±12.0]	2-6374615-5
0.53	0.23	20.00±0.30 [787.0±12.0]	2-6374615-0
0.50	0.20	15±0.15 [590.6±6.0]	1-6374615-5
0.50	0.20	0.50±0.03 [19.7±1.0]	1-6374615-2
0.50	0.20	10.67±0.15 [420.0±6.0]	1-6374615-1
0.50	0.20	10±0.15 [393.7±6.0]	1-6374615-0
0.50	0.20	9.00±0.15 [354.3±6.0]	6374615-9
0.50	0.20	8.00±0.15 [315.0±6.0]	6374615-8
0.50	0.20	7.00±0.08 [275.6±3.0]	6374615-7
0.50	0.20	6.00±0.08 [236.2±3.0]	6374615-6
0.50	0.20	5.00±0.08 [196.9±3.0]	6374615-5
0.50	0.20	4.00±0.08 [157.5±3.0]	6374615-4
0.50	0.20	3.00±0.05 [122.8±2.0]	6374615-3
0.50	0.20	2.00±.05 [78.7±2.0]	6374615-2
0.50	0.20	1.00±0.05 [39.4±2.0]	6374615-1
SC	LC	L	PART NUMBER
1. MAX IL (dB)			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
C.S.VASU
15SEP05

CHK
J.DUNCAN
15SEP05

APVD
J.DUNCAN
15SEP05

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

AMP

Tyco Electronics Corporation
Harrisburg Pa, 17105-3608

NAME

CABLE ASSEMBLY, FIBER OPTIC
LC TO SC DUPLEX, 62.5 /125

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C=6374615

—

SCALE

NTS

SHEET

1

OF

1

REV

B