


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		K1	REVISED PER ECO-11-004835	11MAR11	RK	HMR



- 1 FOR MINI-APPLICATOR.
- 2 FOR HAND TOOL USE ONLY.
3. WIRE RANGE OF 22-26, INSULATION RANGE OF .040-.050.
4. GOLD PLATING MAY NOT APPEAR ON CARRIER STRIP.
- 5 GOLD PLATING PER MIL-G-45204.
NICKEL PLATING PER QQ-N-290.
TIN PLATING PER MIL-T-10727.
- 6 GOLD PLATED IN LOCALIZED GOLD PLATE AREA AS FOLLOWS:
.000030 MIN GOLD IN MATED AREA,
GOLD FLASH ON REMAINDER OF CONTACT, ALL OVER
.000050 MIN NICKEL UNDERPLATE.
OR
GOLD FLASH OVER
PALLADIUM-NICKEL PLATE, .000030 MIN TOTAL IN MATED AREA,
GOLD FLASH ON REMAINDER OF CONTACT, ALL OVER
.000050 MIN NICKEL UNDERPLATE.
- 7 .000001 MIN GOLD OVER
.000030 MIN NICKEL.
- 8 GOLD PLATED IN LOCALIZED GOLD PLATED AREA,
.000001 MIN GOLD IN MATED AREA,
TIN PLATED WIRE BARRELS, OVER
.000030 NICKEL.
- 9 GOLD PLATED IN LOCALIZED GOLD PLATED AREA,
.000030 GOLD IN MATED AREA,
TIN PLATED WIRE BARRELS, OVER
.000050 NICKEL.

OBsolete	SMALL PACK	7	2	LOOSE PIECE	1-745254-7
OBsolete	STANDARD	9	2	LOOSE PIECE	1-745254-6
OBsolete	STANDARD	9	1	STRIP	1-745254-4
OBsolete	STANDARD	8	2	LOOSE PIECE	1-745254-3
OBsolete	STANDARD	8	1	STRIP	1-745254-1
	STANDARD	7	2	LOOSE PIECE	745254-7
	STANDARD	6	2	LOOSE PIECE	745254-6
	STANDARD	7	1	STRIP	745254-3
	STANDARD	6	1	STRIP	745254-2
PACKAGING TYPE		FINISH	USE	TYPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.WELDON 9-9-86		 TE Connectivity	
		CHK C.RICHARD 9-9-86			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME PIN CONTACT, SIZE 20 DF, 22-26 AWG, W/.040-.050 DIA INSULATION SUPPORT	
		APVD V. KUMAR 9-10-86 PRODUCT SPEC —			
		APPLICATION SPEC 114-10000		RESTRICTED TO —	
MATERIAL BRASS PER MIL-C-50		FINISH  SEE TABLE		SIZE A2	
		WEIGHT —		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-745254	
				SCALE 10:1	
				SHEET 1 of 1	
				REV K1	