



| LOC | | DIST | | REVISIONS | | | | | | |
|-----|--|------|--|-----------|-----|----------------------|--|---------|-----|------|
| HM | | 00 | | F | LTR | DESCRIPTION | | DATE | OWN | APVD |
| | | | | | B | REV; EC 0B40-0087-01 | | 27APR01 | GG | BT |


- 

DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- 

MATERIAL: CONNECTOR HOUSING - ABS MOLDING COMPOUND, NATURAL.
EDGE CONNECTOR HOUSING - POLYESTER MOLDING COMPOUND, BLACK.
EDGE CONNECTOR TERMINALS - COPPER SILICON TIN CHROME ALLOY WITH 1.02µm [0.000040]
MINIMUM GOLD PLATE OVER 1.27µm [0.000050]
MINIMUM NICKEL PLATE IN CONTACT AREA, GOLD FLASH OVER REST OF TERMINAL.
SCREWS - ZINC PLATED CARBON STEEL.
DUST COVER - 0.25 [0.010] THICK CLEAR PVC.
3.





EDGE CONNECTOR AND STUFFER ASSEMBLIES SHIPPED NOT ASSEMBLED.
4.

STEEL CITY 4" SQUARE DEVICE COVER FOR TWO DEVICES - CATALOG SERIES 52-C (OR AMP APPROVED EQUIVALENT) IS RECOMMENDED FOR PROPER INSTALLATION WHEN DOUBLE GANG APPLICATION IS REQUIRED.



406352-1

PART NUMBER

| | | | | | | | |
|--|--|---|-----------|---|--|--|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHALL BE CONTACTED FOR THE LATEST REVISION. | | DWN DL DRUMMOND | 05 DEC 96 | AMP AMP Incorporated Harrisburg, PA 17105-3608 | | | |
| DIMENSIONS: mm [INCHES] | | CHK DL DRUMMOND | 12 FEB 97 | | | | |
|  | | APVD A. DUNN | | NAME WALLBOX KIT, DUAL, UNSHIELDED, AMP COMMUNICATIONS OUTLET | | | |
| | | PRODUCT SPEC 108-1206 | | SIZE A1 00779 | | | |
| | | APPLICATION SPEC | | CAGE CODE C-406352 | | | |
| | | MATERIAL  | | DRAWING NO C-406352 | | | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: | | FINISH  | | WEIGHT - | | | |
| 0 PLC ±.00 | |  | | CUSTOMER DRAWING | | | |
| 1 PLC ±.00 | | | | SCALE 2:1 | | | |
| 2 PLC ±.00 | | | | SHEET 1 OF 1 | | | |
| 3 PLC ±.00 | | | | REV B | | | |
| 4 PLC ±.00 | | | | | | | |
| ANGLES | | | | | | | |