





LOC	DIST	REVISIONS				
HM	00	P	LTR	DESCRIPTION	DATE	APVD
			S	REV PER ECO-09-001811	30JAN09	LH JJ
			T	REACTIVATE -1, REV ECO-09-016232	10JUL09	LH JJ



UNCRIMPED



CRIMPED

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.

2 MATERIAL: HOUSING - THERMOPLASTIC (CLEAR)
TERMINAL - TIN PLATED PHOSPHOR BRONZE

3. WIRE RANGE: 19-26 AWG SOLID COPPER CONDUCTORS.

4 SEALANT ADDED TO HOUSING IN THREE AREAS.

5. FOR CRIMPING INFORMATION SEE APPLICATION SPECIFICATION 114-6010.

6 MATERIAL: HOUSING - THERMOPLASTIC (YELLOW)
TERMINAL - PHOS BRZ

7 MATERIAL: HOUSING - THERMOPLASTIC (CLEAR)
TERMINAL - PHOS BRZ

8 MATERIAL: HOUSING - THERMOPLASTIC (YELLOW)
TERMINAL - TIN PLATED BRASS

OBSOLETE	1000	6	WITH SEALANT	1-552795-8
	5	2	WITH SEALANT	1-552795-7
	BULK	6	WITHOUT SEALANT	1-552795-5
OBSOLETE	100	6	WITHOUT SEALANT	1-552795-4
	100	7	WITH SEALANT	1-552795-2
	500	7	WITH SEALANT	552795-6
OBSOLETE	BULK	7	WITH SEALANT	552795-5
	1000	6	WITHOUT SEALANT	552795-4
	1000	8	WITHOUT SEALANT	552795-3
OBSOLETE	1000	7	WITH SEALANT	552795-2
	1000	2	WITH SEALANT	552795-1
	1000	2	WITH SEALANT	552795-1
PARTS PER CONTAINER		DESCRIPTION		PART NUMBER

SUPSD BY 552795-4

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. HALL 20FEB04	Tyco Electronics Corporation Harrisburg, Pa 17105-3608		
DIMENSIONS: INCHES		CHK A. KINKA 24FEB04			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. KINKA 24FEB04	NAME		
0 PLC ± -		PRODUCT SPEC	TEL-SPLICE ASSEMBLY, 2 WIRE (INTERNATIONAL)		
1 PLC ± -		APPLICATION SPEC	-		
2 PLC ± -		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=552795
3 PLC ± .005		CUSTOMER DRAWING	SCALE 10:1	SHEET 1 OF 1	REV T
4 PLC ± -					
ANGLES ± -					
FINISH -					

.262	24-26
.276	19-22
DIM "A" MAX	WIRE-AWG