


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVO
HM	00		B	REDWN & REV; EC 0B40-0061-01	30MAR01	LH	GB
			C	REV-EC0-06-007951	05APR06	LH	GB
			D	REV EC0-10-011451	01JUN2010	LH	RA



RECOMMENDED MOUNTING DIMENSIONS



MOUNTING:

A)WALL: SINGLE OR DOUBLE GANG ELECTRICAL BOXES, FURNITURE PANELS, DESKS, SURFACE ACCESSIBLE RACEWAYS, FLAT SURFACE.
B)FLOOR: CELLULAR PRESETS OR POKE-THRUS, UNDERCARPET WIRING.

10. SHIPPING WEIGHT: 0.46 POUNDS PER ASSEMBLY.
11. TWO LABELS, LABEL COVER AND FOUR 6-32 X .88 [22.35] LONG SELF-TAPPING MOUNTING SCREWS ARE PACKAGED INSIDE MOUNT OUTLET ASSEMBLY.



DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.

2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS.

3. DESCRIPTION: A WORKSTATION OUTLET CAPABLE OF DISTRIBUTING COAX, FIBER, AND TWISTED PAIR. THE OUTLET CAN EASILY BE RECONFIGURED TO ACCOMODATE THE APPLICATION NEEDS.



MATERIAL: BASE, COVER, ICON WHEEL AND INSERTS - ABS MOLDING COMPOUND, 94V-0 RATED. SEE TABLE FOR COLOR. LABEL COVER - POLYCARBONATE MOLDING COMPOUND, CLEAR. SCREWS - ZINC PLATED CARBON STEEL. PRESS-IN INSERT - STAINLESS STEEL.


5. FEATURES:

A) ACCOMODATES FIBER OPTIC, COAXIAL, AND TWISTED PAIR MEDIA.
B) EIGHT PORT INTERCHANGABLE INSERTS.
C) SUPPORTS AMP NETCONNECT® SYSTEMS.
D) CONTROLLED STORAGE FOR 2-3 FEET EACH OF TWO DUAL FIBER CABLES AT MINIMUM REQUIRED RADIUS.

6. APPROVALS: N/A






7. ELECTRICAL PARAMETERS: UL FILE E81956, CSA FILE LR7189.

8. PACKAGING: ONE ASSEMBLY PER PRINTED POLYBAG.



INSERT
8 REQUIRED

OBSOLETE	NEMA GRAY	557366-3
	LIGHT ALMOND	557366-1
	COLOR	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. HALL 28MAR01		 Tyco Electronics Corporation Harrisburg, PA 17105-3608			
		CHK G. BOWMAN 30MAR01					
DIMENSIONS: INCHES [mm]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD G. BOWMAN 30MAR01		NAME	
		0 PLC ± - 		SURFACE MOUNT OUTLET ASSEMBLY —			
		1 PLC ± -					
		2 PLC ± -					
		3 PLC ± -		PRODUCT SPEC —			
		4 PLC ± -					
		ANGLES ± -		APPLICATION SPEC 408-3281			
MATERIAL - 		FINISH - 		WEIGHT —		RESTRICTED TO —	
CUSTOMER DRAWING						SIZE A2	
						CAGE CODE 00779	
						DRAWING NO C=557366	
						SCALE 1:1	
						SHEET 1 of 1	
						REV D	