





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	52		E1	REVISED PER ECO-11-005027	12MAR11	RK	HMR

D


C

B


A



RECOMMENDED CUT OUT
FOR 1.73 [.068] MAX THICK PANEL
SCALE 1:1



40.89
[1.610]



- MATES WITH HOUSING 640516.
- UL LOGO AND CSA LOGO TO APPEAR ON EITHER LATCH SURFACE PER AMP SPEC 202-20, I.D. NO. 1-18838-3 AND 1-18839-3. FROST BACKGROUND OPTIONAL.
- DIMENSIONS IN BRACKETS ARE IN INCHES.
- NON-FILL PERMITTED UP TO 3.8 [.15] FROM EDGE OF LATCH ARM ON THE 0.38 [.015] THICK FLANGE, 4 PLC.

D

C

B

A

640526

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. VESTAL 12-01-97	 TE Connectivity						
DIMENSIONS: mm [INCHES]		CHK R. SWING 12-01-97							
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. BEDDICK 12-01-97	NAME HOUSING, PLUG MRII 36 POSITION					
	0 PLC ± —		PRODUCT SPEC						
	1 PLC ± —		—						
	2 PLC ± 0.13[.005]		APPLICATION SPEC						
	3 PLC ± —		—						
4 PLC ± —		—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
ANGLES ± 0° 30'		—	A2 00779 C-640526				—		
MATERIAL NYLON UL 94V-0 NATURAL (BRICK RED)	FINISH —	WEIGHT —	CUSTOMER DRAWING				SCALE 4:1	SHEET 1 of 1	REV E1