

# Sentry Switched CDU

## Key Features

- > Remote Power Management: Power cycle individual power outlets, or groups of power outlets, to remotely reboot servers and network devices, anywhere in the world. Or, power-off unused power receptacles
- > High Power Distribution: 3-Phase power; 20 or 30-Amp power input feed options
- > High Density: Single power input feed; 24 outlets per enclosure
- > IP Access & Security: Web interface, SSL, SSH, Telnet, SNMP, FTP, SNMP, Syslog, LDAP, LDAPS, TACACS and RS-232 access
- > Add an Expansion Module: Daisy chain the Switched CDU Expansion Module (CW/CX) for power management of separate power circuits from a single IP address
- > Environmental Monitoring: Each Switched CDU supports two temperature & humidity probes and reports conditions thru the Web interface
- > Enterprise View: View and access multiple Switched CDUs from one Web interface\*\*
- > SNMP Traps: Provide automated alerts for power and environmental conditions
- > Input Current Monitor: Precisely measure the aggregate current draw (in amps) on each power circuit. On-site verification of the input current with the LED digital display. Remote verification via browser or serial screen.
- > Power-up Sequencing: Prevent an in-rush power overload

## CW-24VD/Y

### High-Density Power Distribution

The Switched CDU's combine remote configuration and management with power distribution and power and environmental monitoring. Reboot a single or dual-power server with one command. Receive SNMP-based alerts and email alerts when power or environmental conditions exceed thresholds. Assign users specific access rights to designated outlets or groups.

Only the Switched CDU products provide the flexibility needed for all data centers and remote sites, including power requirements for high-amp, high voltage; UL 60950-1 branch circuit protection; SSL & SSH security; and SNMP-based input current monitoring.

The Switched CDU also supports Enterprise View PDU Manager. This gives the engineer the ability to manage a large installation of Networked CDUs from one location, view and access multiple Smart and Switched CDUs from a single web interface.

### Additional Benefits:



#### Branch Circuit Protection

The Sentry CDU Family meets the new UL 60950-1 requirement for branch circuit protection.

**Attention!** The Sentry CDU products meet the above criteria by providing overcurrent protection with UL-listed Bussman SC fuses for each branch circuit.



#### Input Current Monitoring

The CDU's exclusive True RMS current monitoring is critical to preventing overloads in high-density computing environments. LED digital displays on the CDU enclosure report the input current of each phase or branch circuit.



#### Temperature and Humidity

The Switched CDU supports two external probes. Each of these probes measure both temperature and humidity. Receive SNMP-based alert notifications when conditions exceed defined thresholds.



Model	Available Input Voltages	Amperage	Available Input Cord	Outlets	Dimensions** (L x W x D)
CW-24VD-L20M	3-Phase Delta, 208V 50/60Hz	20A	NEMA L15-20P Cordset	(24) IEC 60320/C13	69.0" x 1.75" x 2.25"
CW-24VD-L30M	3-Phase Delta, 208V 50/60Hz	30A	NEMA L15-30P Cordset	(24) IEC 60320/C13	69.0" x 1.75" x 2.25"
CW-24VY-L20M*	3-Phase Wye, 208V 50/60Hz	20A	NEMA L21-20P Cordset	(24) IEC 60320/C13*	69.0" x 1.75" x 2.25"
CW-24VY-L30M*	3-Phase Wye, 208V 50/60Hz	30A	NEMA L21-30P Cordset	(24) IEC 60320/C13*	69.0" x 1.75" x 2.25"

\*This unit has an additional NEMA 5-20R, 110V Utility Outlet

\*\*Please note that the depth of these enclosures are 3.0" deep at the placement of the fuse

## Additional Features and Specifications

### Agency Approvals

- > US & Canada (cTUVus mark) to UL 60950-1:2003 and CAN/CSA 22.2 No. 60950-1-03
- > European Union (TUVGS mark) to EN 60950-1:2001
- > FCC Class A, Part 15
- > CE
- > EMC - EN 55022 Class A, EN 55024

### Communications and Security

- > 10/100 BaseT Ethernet
- > HTTP/HTTPS
- > SSLv3/TLSv1
- > SNMPv2
- > SSHv2
- > Telnet
- > LDAPv3
- > LDAPS
- > TACACS+
- > RS-232 (Serial)

### Branch Circuit Protection

- > Compliant to UL 60950-1

### Power Cord Options

- > PTCORD-1 IEC 60320/C19 - NEMA L6-20P , 10'(3m)
- > PTCORD-2 IEC 60320/C19 - Schuko 10'(3m)
- > PTCORD-3 IEC 60320/C19 - IEC 60309 (BS4343, CEE17) 16/20A Blue (UK Commando) 10'(3m)
- > PTCORD-4 IEC 60320/C19 - BS1363 13A (UK) 10'(3m)

### Accessories

- > Optional Temperature & Humidity Probe
  - EMTH-1-1 Temperature & Humidity Probe, 10ft (3m)
- > Environmental Monitor
  - EMCU-1-1B allows up to (2) additional temperature & humidity probes, (1) water sensor, (4) dry contact closures, (1) analog-to-digital contact sensor. Includes (1) temperature/humidity probe with unit.
- > SPM (Sentry Power Manager) Appliance:
  - Monitor and Manage multiple Sentry CDU's
  - Monitor and Manage all alarm conditions
  - Reporting and Trending
  - Group or Cluster outlets for reboot and power information



### Expansion Module

#### Model Numbers

- > CX-24VD-L20M
- > CX-24VD-L30M
- > CX-24VY-L20M
- > CX-24VY-L30M



## Server Technology

**HEADQUARTERS - NORTH AMERICA**  
 Server Technology, Inc.  
 1040 Sandhill Drive  
 Reno, NV 89521  
 United States  
 1.775.284.2000 Tel  
 1.775.284.2065 Fax  
 sales@servertech.com  
 www.servertech.com  
 www.servertechblog.com

**EMEA**  
 Server Technology Intl  
 United Kingdom  
 +44 (0) 1628 509053 Tel  
 +44 (0) 1628 509100 Fax  
 salesintl@servertech.com

**APAC**  
 Server Technology Intl  
 37th Floor, Singapore Land Tower  
 50 Raffles Place  
 Singapore 048623  
 +65 (0) 6829 7008 Tel  
 +65 (0) 6234 4574 Fax  
 salesintl@servertech.com