




LOC	DIST	REVISIONS			GG	EL	DATE	DWN	APVD
		P	LTR	DESCRIPTION					
HM	00		R	REV PER ECO-12-012918			09JUL2012	JM	JG



1. ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY UNLESS OTHERWISE SPECIFIED.

2. MATERIAL: HOUSING—POLYCARBONATE CLEAR.
TERMINAL— 0.36[.014] THICK PHOS BRONZE PLATED WITH 1.27um[.000050] MINIMUM THICK GOLD IN LOCALIZED GOLD PLATE AREA, OVER 2.54um [.000100] MINIMUM THICK NICKEL UNDERPLATE.



3. PLUG WILL EXCEPT 26 OR 28 AWG STRANDED OR TINSEL WIRE HAVING A MAXIMUM INSULATION OF $\phi 0.99[.039]$ AND A MAXIMUM OVAL CABLE JACKET OF $2.29 \times 4.06 [.090 \times .160]$.

4. TERMINATED DIMENSION TO MEET FCC REQUIREMENTS $.237 \pm .005$.

5. REELED PRODUCT ON STRIP DOES NOT HAVE VOID CORING ILLUSTRATED ON THIS DRAWING.

SUPSD BY 5-641333-2	1000 PER PACKAGE		5-641333-2	
	REELED 5		641333-1	
		DESCRIPTION		PART NO.
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. HALL 20FEB2007	TE Connectivity	
		CHK C. DOOLEY 20FEB2007		
DIMENSIONS: INCHES		APVD C. DOOLEY 20FEB2007	NAME MODULAR PLUG ASSEMBLY, 2 POSITION, LINE STRANDED WIRE	
		PRODUCT SPEC 108-1163		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-6016	SIZE A2	
		WEIGHT -		
MATERIAL -		CUSTOMER DRAWING	SCALE 5:1	SHEET 1 of 1
			REV R	