


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CE	16		C2	REVISED-ADDED -24, -25	09NOV07	JWD	JD
			C3	REVISED-ADDED -20	18AUG09	JS	JS

- 1

MAXIMUM INSERTION LOSS, FOR SC AND LC CONNECTORS, IS 0.50 dB PLUS CABLE ATTENUATION OF 1.50 dB/km @ 1300nm (SEE TABLE)
2.

PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702



0.53	25.00±0.30 [984.25±12.00]	2-6754384-5
0.53	24.00±0.30 [944.88±12.00]	2-6754384-4
0.53	20.00±0.20 [787.4±7.87]	2-6754384-0
0.52	10.00±0.15 [393.7±6.0]	1-6754384-0
0.51	8.00±0.15 [315.0±6.0]	6754384-8
0.50	5.00±0.08 [196.9±3.0]	6754384-5
0.50	4.00±0.08 [157.5±3.0]	6754384-4
0.50	3.00±0.05 [118.11±2.00]	6754384-3
0.50	2.00±0.05 [78.74±1.97]	6754384-2
0.50	1.00±0.05 [39.40±1.97]	6754384-1
1 MAX IL(dB)	L METERS [INCHES]	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.S.VASU	24SEP05	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: METERS [INCHES]		CHK J.DUNCAN	24SEP05	NAME	
		APVD J.DUNCAN	24SEP05	CABLE ASSEMBLY, FIBER OPTIC, 50/125um XG, 1.8mm OFNP ZIPCORD SC DUPLEX TO LC DUPLEX	
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE A2	
MATERIAL		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH		DRAWING NO C-6754384	
		APPLICATION SPEC		RESTRICTED TO	
		WEIGHT		REV C3	
		CUSTOMER DRAWING		SCALE NTS	
				SHEET 1 OF 1	