

Plantronics Discovery™ 655 Bluetooth® Headset with DSP

Enjoy unparalleled style, mobility and sound clarity with the premium DSP Bluetooth headset

The Plantronics Discovery 655 Bluetooth headset fuses cutting-edge technology with a sleek, ultra-light and discreet design to deliver a mobile experience unlike any other. With Digital Signal Processing (DSP)—the latest in audio technology—the Plantronics Discovery 655 reduces noise levels to provide enhanced sound for clear conversations. It weighs only 9 grams and comes with an innovative AAA charging pocket that provides up to 10 hours of talk time and includes a unique vibrate ring indicator. The Plantronics Discovery 655 sets the standard for style, mobility, and performance.

- Digital Signal Processing (DSP) lets you be heard like never before by actively reducing transmitted background noise, resulting in crystal clear conversations
- The small, ergonomic design provides long-wearing comfort and weighs only 9 grams
- An innovative charging pocket provides a convenient and secure way to charge, store and transport the headset. This unique charging pocket stores a AAA battery that charges the headset between calls—a Plantronics industry first—for up to 10 hours of talk time, and vibrates to indicate incoming calls
- Sleek design and personalized fit with three sizes of soft gel ear tips. Optional ear stabilizer fits securely over the ear
- Headset can be worn in right or left ear
- Mini USB headset charger allows you to easily recharge from a computer
- Supports last number redial and voice-activated dialing for easy mobile use¹
- Freedom to roam up to 33 feet from your Bluetooth device



>>> >> Plantronics Discovery™ 655 Bluetooth Headset
with Digitally Enhanced Sound for Clear Conversations



Discovery 655 Key Features

Talk Time ²	Up to 3.5 hours, increasing to 10 hours with AAA charger
Standby Time	Up to 80 hours
Range	Bluetooth standard 33 feet (10 meters)
Headset Weight	9 grams
Headset Controls ¹	Volume, mute, last number redial, voice-activated dialing, vibrates in pocket
Battery Type	Lithium Ion
Wireless Compatibility	Bluetooth devices supporting headset and hands-free profiles
Version	Bluetooth 2.0
AC Adapter	100–240V

¹Last number redial and voice-activated dialing must be supported by your device or cellular provider.

²Performance may vary by device.

³AC adapter must terminate in a mini USB port in order to be compatible.



Digital signal processing reduces background noise so your voice is transmitted clearly to your caller, even in noisy environments.



One-touch call-control button

Innovative headset weighs only 9 grams

Soft gel ear tips in three sizes for optimal fit and comfort



Optional ear stabilizer offers added security



Carrying pocket provides convenient and secure storage—plus a unique vibrate ring indicator



AAA battery charger extends your talk time up to 10 hours



Use mini USB adapter to charge from your PC or mobile phone AC adapter³



PLANTRONICS
SOUND INNOVATION™



For more information about the Discovery 655 or other Plantronics products, please visit our Web site at: www.plantronics.com

TEL: 800-544-4660 (USA AND CANADA)
831-458-7700 (OUTSIDE USA)

© 2006 Plantronics, Inc. All rights reserved. Plantronics, the logo design, Plantronics Discovery and Sound Innovation are trademarks or registered trademarks of Plantronics, Inc. The Bluetooth word mark and logos are owned by Bluetooth SIG, Inc., and any use of such marks by Plantronics, Inc. is under license. All other trademarks are the property of their respective owners. Space photo imagery courtesy of NASA. Printed 07/06 MPS-13

Sound Innovation for missions to the moon. And for everyday life on this planet, too.

In 1969, a Plantronics headset carried the historic first words from the moon: "That's one small step for man, one giant leap for mankind." Today, we're the headset of choice in mission-critical applications such as air traffic control and 911 dispatch. This history of proven sound innovation is the basis for every product we build—whether it's for work, for home or on the go.

