

Arecont Vision

AV3155 (3 Megapixel Color Camera with Integrated 4.5-10mm Lens)

AV3155DN (3 Megapixel Day/Night Camera with Integrated 4.5-10mm Lens)

AV3155-16 (3 Megapixel Color Camera with Integrated 8-16mm Lens)

AV3155DN-16 (3 Megapixel Day/Night Camera with Integrated 8-16mm Lens)

Architect & Engineering Specifications

Version 083010



Arecont Vision
425 East Colorado Street
7th Floor
Glendale, CA 91205

1.818.937.0700

<http://www.arecontvision.com/>

PART 1 - NOT USED

PART 2 - PRODUCTS

2.01 Megapixel camera

A. Functional Description

1. The AV3155 MegaDome™ series network camera is part of Arecont Vision's full line of H.264 megapixel cameras. This fully compliant implementation of H.264 (MPEG 4, Part 10) provides full 2048 x 1536 megapixel resolution at full video frame rates of 15fps. The MegaDome™ camera line provides an all-in-one solution with integrated megapixel camera, lens, and vandal resistant dome enclosure. Using MegaVideo® technology, these cameras offer bandwidth and storage efficiency of up to 10X on average over traditional megapixel counterparts.

The AV3155 is a high sensitivity, PoE (IEEE 802.3af) compliant camera with color and Day/Night configurations. Built with Arecont Vision's proprietary massively-parallel MegaVideo® technology, the AV3155 has the ability to output multiple image formats allowing the simultaneous viewing of the full resolution field of view and regions of interest for high definition forensic zooming. This camera offers over ten times the resolution of standard resolution IP cameras with the ability to output full real time frame rates.

B. Detailed Specifications

1. The camera shall utilize a high sensitivity 3 Megapixel CMOS sensor with 1/2" optical format
2. The camera shall have and integrated 4.5-10mm megapixel IR corrected varifocal lens with 1/2" optical format, F1.8. (AV3155 and AV3155DN only)
3. The camera shall have and integrated 8-16mm megapixel IR corrected varifocal lens with 1/2" optical format, F1.8. (AV3155-16 and AV3155DN-16 only)
4. The camera shall have a dome enclosure complying with IP66 weatherproofing standards
5. The camera dome chassis shall be vandal resistant constructed of aluminum with a 4" polycarbonate dome bubble

Model AV3155

6. The camera shall have a 3-axis gimbal with 360° pan 90° tilt and 180° Z-rotation for easy and accurate positioning
7. The camera shall be surface mount with optional pendant mount or wall mount
8. The camera shall be H.264 (MPEG4,Part 10) compliant
9. The camera shall have dual standard compression support with simultaneous streaming of both H.264 and MJPEG formats
10. The camera shall have multi-streaming support of up to 8 non-identical concurrent streams (different frame rate, bit rate, resolution, quality and compression format)
11. The camera's bit rate control shall be selectable from 100 Kbps to 10 Mbps for each independent stream
12. The camera shall have Real Time Streaming Protocol (RTSP) support allowing for compatibility with media players such as Windows Media Player, Apple QuickTime, VLC Player and others
13. The cameras H.264 implementation shall maintain full real time video frame rates
14. The camera shall output at a maximum resolution of 2048(H) x 1536(V) pixels at a maximum frame rate of 15 frames per second (FPS)
15. It shall be possible to program the camera to output a variety of lower resolution images. i.e. 1280(H) x 1024(V) pixels at 32 FPS, or 1600(H) x 1200(V) pixels at 24 FPS
16. The camera shall feature streaming of the full field of view (FOV) and simultaneous multiple regions of interest (ROI) for forensic zooming
17. The camera shall be equipped with a 100 Mbps LAN connector and can deliver image data at an unthrottled maximum data rate of up to 55 Megabits per second (55 Mbps)
18. The camera shall provide 21 levels of compression quality for optimal viewing and archiving
19. The camera shall support a minimum TFTP, HTTP, RTSP, RTP over TCP and RTP over UDP network protocols
20. The cameras shall feature precision motion detection with a minimum of 64 detection zones
21. The camera shall feature automatic exposure, automatic multi-matrix white balance, shutter speed control, 50/60Hz selectable flicker control,

Model AV3155

programmable brightness, saturation, gamma, sharpness, windowing and decimation, simultaneous delivery of full-field of view and zoomed images at video frame rate, instantaneous electronic zoom, pan and tilt and electronic image rotation by 180 degrees

22. The camera shall incorporate necessary algorithms and circuits to detect motion in low light with clarity
23. The camera shall support a minimum illumination of 0.2 Lux @ F1.4 in color mode
24. The camera shall support an IR sensitive minimum illumination of 0 Lux in B/W mode (DN version only)
25. The camera's primary power source shall be Power over Ethernet (PoE) complying with the IEEE 802.3af standard
26. The camera shall have the alternative option to be powered from between a 12V DC up to 48V DC or 24V AC power source providing at least 5W of power.
27. The camera's operating ambient temperature shall be -30°C (-22°F) to 50°C (122°F) for warm start conditions
28. The camera shall be FCC Part 15, Class A, CE and RoHS compliant
29. The camera shall have total unit dimensions of Ø5.5 x 4.9 H (in), Bubble only: Ø4.0 x 2.4 H (in)
30. The camera shall have a total unit weight of: 2.0 lbs (0.91 kg)

C. Technical Description

1. The Megapixel Camera shall meet the following minimum requirements:

Operational

Imaging	3 megapixel CMOS image sensor
	2048(H) x 1536(V) pixel array
	1/2" optical format
	3.2 μ m pixel pitch
	Bayer mosaic RGB filter

Minimum illuminationColor: 0.2 Lux @ F1.4

Day/Night: 0 Lux, IR sensitive

Dynamic range	61 dB
---------------	-------

Maximum SNR	49 dB
-------------	-------

Full Field of View (FOV) Resolutions

2048(H)x1536(V) 3 megapixel

1024(H) x768(V) 1/4 resolution

Cropped Field of View Resolutions

1920x1200 WUXGA

1920x1080 HDTV-1080p

1600x1200 2 MP

1280x1024 1.3 MP

1280x720 HDTV-720p

1024x768 XGA

Model AV3155

800x600 SVGA

704x570 PAL

704x480 NTSC

640x480 VGA

352x288 CIF

320x240 SIF

Data Transmission

Video frame rate up to 15fps @ 2048x1536

20fps @ 1920x1200

22fps @ 1920X1080

24fps @ 1600x1200

32fps @ 1280x1024

Compression type H.264 (MPEG4, Part 10)

Motion JPEG

21 levels of quality

TFTP, HTTP, RTSP, RTP over TCP, RTP over UDP image transmission protocols

100Base-T Ethernet Network Interface

Data rate Bit rate control from 100 Kbps to 10 Mbps

Unthrottled data rate up to 55 Mbps

Multi-streaming: 8 non-identical streams

Programmability

Auto Exposure (AE) and Gain Control (AGC) >120dB

On-camera real-time motion detection with 64 detection zones

Auto backlight compensation

Model AV3155

Auto multi-matrix white balance

50/60Hz selectable flicker control

Electronic pan, tilt, zoom (PTZ)

Electronic image flip - 180 degree rotation

Resolution windowing down to 32x32 pixels window

Programmable shutter speed to help control motion blur

MoonLight™ mode - extended exposure for enhanced low light performance

Proprietary noise cancellation

Programmable resolution, brightness, saturation, gamma, sharpness, tint

Picture-in-Picture: simultaneous delivery of full field of view and zoomed images

Bandwidth & storage savings by running at 1/4 resolution

Electrical

General purpose opto-coupled input and output

Power over Ethernet (PoE): PoE 802.3af

DC input: auxiliary 12 V – 48 V DC

AC input: auxiliary 24 V AC

Power consumption 5 Watts maximum

Regulatory

FCC, Class A

CE and RoHS compliant

Environmental

Model AV3155

IP66 weatherproofing standard

Operating temperature Warm Start: -30°C (-22°F) to +50°C (122 °F)

Cold Start: 0°C (32 °F) to +50°C (122 °F)

Storage temperature -20°C (-4 °F) to +60°C (140 °F)

Humidity 0% to 90% (non condensing)

Mechanical

3-axis camera gimbal with 360° pan 90° tilt and 180° Z-rotation

Die-cast aluminum chassis with 4" polycarbonate dome bubble

Total unit dimensions: Ø5.5 x 4.9 H (in), Bubble only: Ø4.0 x 2.4 H (in)

Total unit dimensions: Ø140.3 x 124.6 H (mm), Bubble only: Ø102 x 61.8 H (mm)

2.0 lbs (0.91 kg)

Lens

Integrated 4.5-10mm megapixel IR corrected varifocal lens with 1/2" optical format, F1.8. (AV3155 and AV3155DN only)

Integrated 8-16mm megapixel IR corrected varifocal lens with 1/2" optical format, F1.8. (AV3155-16 and AV3155DN-16 only)

MegaDome™ Accessories

MD-WMT: Wall Mount

MD-PMT: Pendant Mount

MD-PMA: Pole Mount

MD-CRMA: Corner Mount

MD-FMA: Flush Mount

Model AV3155

MD-EBA: Electrical Box Adaptor

Related Documentation

- a. AV User Manual
- b. AV Software Developer Kit Manual
- c. AV1355, AV2155, AV3155, AV5155 Network Camera Specification

D. Model Numbers

1. The camera shall be Arecont Vision model AV3155, 3 megapixel color camera integrated 4.5-10mm IR corrected varifocal lens
2. The camera shall be Arecont Vision model AV3155DN, 3 megapixel Day/Night camera integrated 4.5-10mm IR corrected varifocal lens
3. The camera shall be Arecont Vision model AV3155-16, 3 megapixel color camera integrated 8-16mm IR corrected varifocal lens
4. The camera shall be Arecont Vision model AV3155DN-16, 3 megapixel Day/Night camera integrated 8-16mm IR corrected varifocal lens

E. Warranty

1. Minimum 1 Year parts and labor

Arecont Vision reserves the right to change products or specifications without notice.