




ITEM NO.	DESCRIPTION	QTY.
1	PLATE,FLUSH,6P,W/LABELS	1
2	SCREW,6-32 PAN HD-SPECIAL	2
3	CARD,PAPER,.40X1.92,BLANK	2
4	COVER LABEL,CLEAR	2
5	COVER LABEL,MATCHING COLOR	2

CATALOG NUMBER	COLOR	DESCRIPTION
IFP160W	OFFICE WHITE	PLATE, FLUSH 6 PORT
IFP16EI	ELECTRIC IVORY	PLATE, FLUSH 6 PORT
IFP16W	WHITE	PLATE, FLUSH 6 PORT
IFP16GY	GRAY	PLATE, FLUSH 6 PORT
IFP16TI	TELCO IVORY	PLATE, FLUSH 6 PORT
IFP16BK	BLACK	PLATE, FLUSH 6 PORT
IFP16AL	ALMOND	PLATE, FLUSH 6 PORT
IFP16LA	LIGHT ALMOND	PLATE, FLUSH 6 PORT



KEYSTONE OPENING



- NOTES
UNLESS OTHERWISE SPECIFIED:
- 1. UL LISTED: E129878
 - 2. CSA CERTIFIED: LR 80837
 - 3. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

C	5870	6/8/06	ADDED -LA CATALOG NUMBER	CD	
B	5680	8/23/05	ADDED -AL CATALOG NUMBER	CD	
A	4148	02/22/01	INITIAL RELEASE	PSM	HKM
REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY

Created on AUTOCAD

DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982
UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES (MM).
TOLERANCES
.XX = ±.01 (.25)
.XXX = ±.005 (.127)
.XXXX = ±.0025 (.0635)
ANGLE TOL ±1°

IN ACCEPTING OUR DRAWINGS,
BLUEPRINTS, OR SUPPORTING
DOCUMENTATION FOR QUOTATION
OR OTHER PURPOSES, YOU AGREE
NOT TO DISCLOSE TO OTHERS
THE IDEAS, INFORMATION, OR
DESIGNS SHOWN HEREIN, AND
THAT YOU WILL MAKE NO USE
OF SAME WITHOUT PERMISSION


PROJECT REFERENCE:

MATERIAL:

DRAWN BY:
P.S.MAGUIRE 02/22/2001

CHECKED BY:
H. McGREGOR 02/28/2001

APPROVED BY:
H. McGREGOR 02/28/2001



Hubbell Premise Wiring
HUBBELL INCORPORATED (Delaware)
14 Lord's Hill Road, Stonington, Connecticut 06378

TITLE:
INFINE STATION FACE PLATE
6 PORT, FLUSH
WITH LABEL HOLDERS

SIZE
C

DRAWING NO.
C773067

SCALE:
FULL

SHEET
1 OF 1

REV.
C