

## LRD41C21/LRD41C22 Series Receiver

### COAXITRON®/RS-422 COMPATIBLE, FOR LEGACY® SYSTEMS

#### Product Features

- 64 Presets
- Fixed Speed or Full Pan/Tilt/Zoom (PTZ) Variable Speed Control Models Available
- 8 Inputs for Preset Alarms\*
- 1 Alarm Output\*
- 2 Relay Outputs: Aux 1 and Aux 2\*
- Self-Test Diagnostics
- Auto/Random Scan
- Camera Synchronization
- Serial Com Port (RS-422)
- Coaxitron® Compatible
- Transient Suppression
- NTSC or PAL Video
- Test Local Control (TLC) Capability
- Adjustable Lens Voltages
- For Use with Legacy® LWM41 Wall Mount

The **LRD41C21/LRD41C22 Series** Legacy® receiver is designed for use with our LWM41 wall mount. Standard features include 64 presets, 8 inputs for preset alarms\*, and 1 alarm output. Choose from fixed speed or variable speed models for 24/120/230 VAC applications.

The **LRD41C21 Series** receiver is for use with fixed speed Legacy pan/tilt models PT780P/PP, PT780-24P, PT780-24P/PP, PT780-24SL, and PT780-24SL/PP. The **LRD41C22 Series** receiver is for use with variable speed pan/tilt models PT780-VSSL, PT780-VS/PP, and PT780-VSSL/PP.

The **LRD41C21/LRD41C22 Series** is compatible with either Coaxitron® control systems utilizing standard 15-bit or extended 32-bit command protocols or Pelco serial RS-422 control systems utilizing Pelco D or Pelco P type protocols.

Also available is the **LRD41TLC** test local control module, which allows on-site testing of Legacy system functions. Simply plug the TLC into the connector on the receiver and you are ready to test the system functions. The TLC module operates on +5 VDC supplied by the receiver and controls a variety of functions: iris open/iris close, focus near/focus far, zoom telephoto/zoom wide, tilt up/tilt down, and pan left/pan right.



**LEGACY LWM41 WALL MOUNT  
WITH INTEGRAL RECEIVER**



**LEGACY LRD41A11-1 RECEIVER  
SHOWN WITH LRD41TLC TEST LOCAL CONTROL MODULE**

\*Requires optional LRD41C-CONNKIT



by **Schneider Electric**

International Standards  
Organization Registered Firm;  
ISO 9001 Quality System



C557 / REVISED 3-22-11

# TECHNICAL SPECIFICATIONS

## MODELS

LRD41C21-1	Legacy fixed speed receiver with up to 64 presets, 120 VAC input; use with LWM41 Legacy wall mount
LRD41C21-2	Same as LRD41C21-1 except 24 VAC input
LRD41C21-3	Same as LRD41C21-1 except 230 VAC input
LRD41C22-1	Legacy variable speed receiver with up to 64 presets, 120 VAC input; use with LWM41 Legacy wall mount
LRD41C22-2	Same as LRD41C22-1 except 24 VAC input
LRD41C22-3	Same as LRD41C22-1 except 230 VAC input

## MECHANICAL

RS-422 Connector	4-position connector
Aux/Alarm Connector	18-position double-stack header for interface; Aux/Alarm mating connectors not supplied (refer to <i>OPTIONAL ACCESSORIES</i> )
Video and Sync Connectors	BNC
Pan/Tilt Connector	37-pin connector
Power Connector	6-position (mating connector on switch bracket)

## ELECTRICAL

### Input Voltage

120 VAC Models	LRD41C21-1	LRD41C22-1
Input	120 VAC	120 VAC
Pan/Tilt	120 VAC	12 VDC
Camera	24 VAC	24 VAC
Enclosure	120 VAC	120 VAC
24 VAC Models	LRD41C21-2	LRD41C22-2
Input	24 VAC	24 VAC
Pan/Tilt	24 VAC	12 VDC
Camera	24 VAC	24 VAC
Enclosure	24 VAC	24 VAC
230 VAC Models	LRD41C21-3	LRD41C22-3
Input	230 VAC	230 VAC
Pan/Tilt	120 VAC	12 VDC
Camera	24 VAC	24 VAC
Enclosure	230 VAC	230 VAC

Frequency	60/50 Hz
Video Input	75 ohms terminating
Video Output	75 ohms terminating
Video Bandwidth	10 MHz
Video Gain	Unity
Video Formats	NTSC or PAL
Control Method	Coaxitron, 15-bit and 32-bit protocols or 2-wire RS-422
Standard Baud Rate	
D-type Control	2400 baud only
P-type Control	2400/4800/9600 baud
Alarm In	GND to operate, +5 V or open to disable
Alarm Out	One open collector, TTL 5 VDC, 15 to 25 mA
Aux 1 and 2 Relay	1 A at 24 VDC

Lens Output	
Voltage	6 VDC to 10 VDC
Current	25 mA at 10 VDC, 100 mA at 9 VDC
Operating Distances	Cable distances are approximate according to cable type used. 75-ohm coaxial cable is required.
Coaxitron Version	750 ft (229 m) on RG59/U
RS-422 Version	4,000 ft (1,219 m) on 24 AWG twisted pair (for point-to-point and daisy-chain configurations only)
Fuse Values	F1 Input Power (LRD)
LRD41C21-1	2 A
LRD41C21-2	2.5 A
LRD41C21-3	500 mA
LRD41C22-1	400 mA
LRD41C22-2	1.25 A
LRD41C22-3	160 mA
	F2 Enclosure
	2 A
	6.3 A
	1 A
	2 A
	6.3 A
	1 A

**LRD Input Current Table**

Model	Receiver*	Enclosure/Accessories†
LRD41C21-1	500 mA	1.5 A
LRD41C21-2	2 A	6 A
LRD41C21-3	250 mA	900 mA
LRD41C22-1	200 mA	1.5 A
LRD41C22-2	1 A	6 A
LRD41C22-3	100 mA	900 mA

\*Current required to run the receiver, pan/tilt, camera, and lens.

†Current required for maximum enclosure options (heaters, wiper, blower, defroster, and pan/tilt heater blankets).

## GENERAL

Operating Temperature	0° to 110°F (–18° to 43°C)
Case Dimensions	11.5" L x 4.5" W x 2.75" H (29.21 x 11.43 x 6.98 cm)
Finish	Alodine
Unit Weight	5 lb (2.27 kg)
Shipping Weight	6 lb (2.72 kg)

## CERTIFICATIONS

- CE, Class A (all models)
- FCC, Class A (all except 230 VAC models)

## OPTIONAL ACCESSORIES

LRD41TLC	Test local control module. Receiver plug-in module for on-site testing of Legacy system functions.
LRD41C-CONNKIT	Two 9-pin connectors that interface with the 18-position double-stack Aux/Alarm connector on the receiver. Required to enable the Aux/Alarm capabilities of the receiver.
LWM41	Legacy wall mount.

### Pelco by Schneider Electric

3500 Pelco Way, Clovis, California 93612-5699 United States

**USA & Canada** Tel (800) 289-9100 Fax (800) 289-9150

**International** Tel +1 (559) 292-1981 Fax +1 (559) 348-1120

**www.pelco.com**

Pelco, the Pelco logo, and other trademarks associated with Pelco products referred to in this publication are trademarks of Pelco, Inc. or its affiliates. All other product names and services are the property of their respective companies. Product specifications and availability are subject to change without notice.

©Copyright 2011, Pelco, Inc. All rights reserved.