make.believe

SONY

High-Quality 1080p HD Rapid Dome Camera

- Excellent 1080p HD picture quality, supporting 30 fps at H.264 (1920 x 1080 maximum resolution)
- The Exmor[™] CMOS sensor incorporated to deliver high image quality and low noise
- High-speed 360 degrees endless rotation
- Powerful 20x optical zoom capability









KEY FEATURES

- Excellent 1080p HD picture quality at 30fps.(H.264).
- The Exmor CMOS sensor delivers high quality and low noise images. Exmor
- Three codecs (H.264, MPEG-4, JPEG) and dual-streaming capability.
- High-speed 360 degrees endless rotation.
- Above-the-horizon tilt 15°tilt-up, total tilt range of 210°.



- 20x optical and total zoom ratio of 240x with 12x digital zoom.
- DynaView™— Wide-D technology to handle various lighting conditions in a scene.



* When using Wide-D technology, the maximum frame rate will be 15fps.

- · Optical Day/Night function to switch to Day or Night mode depending on the light level.
- DEPA™ Intelligent Video Analytics system can be set up with a DEPA-enabled recorder.




- Powered by HPoE for simple installation.
- SD memory card slot for an on-board recording capability.*1*2
- Recording Software (RealShot™ Manager Lite) is bundled to start recording and monitoring instantly.
- Smart phone viewer for accessing the camera from a smart phone.
- ONVIF (Open Network Video Interface Forum) Version 1.02 software. NVIF
- *1 The on-board recording function cannot be used simultaneously with the intelligent motion detection function and the tamper alarm function.
- *2 No guarantee or warranty is given against loss or damage to recorded

SPECIFICATIONS

Camora	SNC-ER580
Camera Imaga davias	1/0.0 tune Fumer CMOC
Image device	1/2.8-type Exmor CMOS
Number of effective pixels	Approx. 3.27 Megapixel
Minimum Illumination	Color: 1.7lx (F1.6, shutter 1/30sec, AGC ON, 50IRE[IP]) B/W: 0.3lx (F1.6, shutter 1/30sec, AGC ON, Night Mode, 50IRE[IP])
	B/W: U.SIX (F1.6, SNUTTER 1/3USEC, AGC ON, NIGHT MODE, SUIRE[IP])
	Color: 1.2lx (F1.6, shutter 1/30sec, AGC ON, 30IRE[IP])
F14	B/W: 0.18lx (F1.6, shutter 1/30sec, AGC ON, Night Mode, 30IRE[IP])
Electronic shutter speed	1/1 to 1/10,000 s
Gain control	Auto/Manual (-3 to 28 dB)
Exposure control	Full auto, Shutter priority, Iris priority, Manual
White balance mode	Auto, ATW, Indoor, Outdoor, One-push, Manual, Sodium vapour lamp
Lens type	Auto-focus Zoom Lens
Zoom ratio	Optical zoom 20x, Digital zoom 12x, Total zoom 240x
Horizontal viewing angle	55.4 to 2.9 degrees
Focal length	f=4.7 to 94.0 mm
F-number	F1.6 to F3.5
Minimum object distance	10mm (wide) to 800mm (tele)
Pan angle	360 degrees endless rotation
Pan Speed	300 degrees/s (max)
Tilt angle	210 degrees(with e-flip)
Tilt speed	300 degrees/s (max)
Preset position	256 positions
Tour	5
Camera Features	
Day/Night	Yes
Wide-D	Yes*1 (86 dB)
Noise Reduction	Yes
Image	
Codec image size (H x V)	1920×1080, 1680×1056, 1280×1024, 1440×912, 1280×960, 1376×768,
Codec inage size (ITX V)	1280×800, 1280×720, 1024×768, 1024×576, 800×600, 800×480, 768×576,
	720×576, 704×576, 720×480, 640×480, 640×368, 384×288, 320×240, 320×1
Video compression format	H.264, MPEG-4, JPEG
Video compression format	
Codec streaming capability	Dual streaming
Maximum frame rate	30 fps (H.264) / 20 fps (MPEG-4) / 16 fps (JPEG)
Audio	
Audio compression	G.711/G.726
Scene Analytics	
Intelligent motion detection	Yes
	165
Network	ID A ID (TOD LIDD ADDIOND LOND LITTO LITTO ETD (I') A ANTO DUOD
Protocols	IPv4, IPv6, TCP, UDP, ARP, ICMP, IGMP, HTTP, HTTPS, FTP (client/server), SMTP, DHCP,
	DNS, NTP, RTP/RTCP, RTSP, SNMP(MIB-2)
ONVIF software	Yes (Ver. 1.02)
Number of clients	5
Authentication	IEEE802.1X
Interface	
Ethernet	10BASE-T / 100BASE-TX (RJ-45)
Card slots	SD memory card x 1 (Compatible with the SD/SDHC standards)
Sensor input	x2
Alarm output	xl
External microphone input	Mini-jack (monaural)
Audio line output	Mini-jack (monaural), Max ouput level: 1 Vrms
General	
Weight	3 lb 12 oz (1.7 kg) (including sealing bracket)
	ø 5 7/8 x 7 5/8 inches (147.4 x 190.9 mm)
Dimensions (ø x H mm)	
Power requirements	HPoE (IEEE802.3at compliant), AC24V
Power consumption	Approx. 25W
Operating temperature	23 to 122°F (-5 to +50 °C)
Starting temperature	32 to 122°F (0 to 50 °C)
Storage temperature	-4 to +140°F (-20 to +60 °C)
Safety regulation	
oulery regulation	UL2044, FCC 15B Class A, IC Class A, IEC60950-1, EN55022(A)+EN55024+EN50130-4, VCCI Class A, C-Tick Class A
Systom Dogyiromonto	E1100022(11)TE1100024TE1100100 4, 1001 01033 M, 0-110K 01033 M
System Requirements	Misses & Wisses & VDTM (2014) Description Felikier
Operating system	Microsoft Windows XPTM (32bit) - Professional Edition
	Microsoft Windows Vista™ (32bit) - Ultimate, Business Edition
	Microsoft Windows 7 (32/64bit) - Ultimate, Professional Edition
	Intel Core2 Duo 2.33 GHz or higher
Memory	Intel Core2 Duo 2.33 GHz or higher 2 GB or more Microsoft Internet Explorer® Ver 6.0 Ver 7.0 Ver 8.0
Memory	Intel Core2 Duo 2.33 GHz or higher 2 GB or more Microsoft Internet Explorer® Ver 6.0 Ver 7.0 Ver 8.0
Memory	Intel Core2 Duo 2.33 GHz or higher 2 GB or more Microsoft Internet Explorer® Ver 6.0 Ver 7.0 Ver 8.0
Memory	Intel Core2 Duo 2.33 GHz or higher 2 GB or more Microsoft Internet Explorer® Ver 6.0 Ver 7.0 Ver 8.0
Memory Web browser	Intel Core2 Duo 2.33 GHz or higher 2 GB or more
Memory Web browser	Intel Core2 Duo 2.33 GHz or higher 2 GB or more Microsoft Internet Explorer® Ver. 6.0, Ver. 7.0, Ver. 8.0 Firefox® Ver. 3.5 (Plug-in free viewer only) Safari® Ver. 4.0 (Plug-in free viewer only) Google Chrome® Ver. 4.0 (Plug-in free viewer only)
Processor Memory Web browser Supplied Accessories	Intel Core2 Duo 2.33 GHz or higher 2 GB or more Microsoft Internet Explorer® Ver. 6.0, Ver. 7.0, Ver. 8.0 Firefox® Ver. 3.5 (Plug-in free viewer only) Safari® Ver. 4.0 (Plug-in free viewer only) Google Chrome® Ver. 4.0 (Plug-in free viewer only) CD-ROM (User's quide, supplied programs), Installation manual, Ceiling bracket,
Memory Web browser	Intel Core2 Duo 2.33 GHz or higher 2 GB or more Microsoft Internet Explorer® Ver. 6.0, Ver. 7.0, Ver. 8.0 Firefox® Ver. 3.5 (Plug-in free viewer only) Safari® Ver. 4.0 (Plug-in free viewer only) Google Chrome® Ver. 4.0 (Plug-in free viewer only)

SYSTEM CONFIGURATION



DIMENSIONS Unit: inches (mm) SONY 7 5/8 (190.9) 7 1/2 (190)

© 2011 Sony Electronics Inc. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. Weights and measurements are approximate. Sony, Sony make. believe, IPELA, Exmor, DEPA, RealShot, and DynaView are trademarks of Sony.

Windows, XP, and Vista are trademarks of Microsoft Corporation.

Core is a trademark of Intel Corporation.

^{*1} When using Wide-D technology, the maximum frame rate will be 15fps.

*The SNC-ER580 includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (http://www.openssl.org/).