

Sentry Switched CDU

Key Features

- > **Remote Power Management:**
Power cycle individual power outlets, or groups of power outlets, to remotely reboot servers and network devices, anywhere in the world. Or, power-off unused power receptacles
- > **High Power Distribution:**
208V, 20A or 30A; 230V 16A or 32A power input feed options
- > **High Density:** Single power input feed; 16 outlets per enclosure
- > **IP Access & Security:** Web interface, SSL, SSH, Telnet, SNMP, FTP, SNMP, Syslog, LDAP, LDAPS, RADIUS, TACACS, RS-232 access
- > **Add an Expansion Module:**
Connect the Switched Expansion CDU (CX) to a Master unit (CW) for power management of separate power circuits from a single IP address
- > **Environmental Monitoring:**
Each Switched CDU supports two temperature & humidity probes and reports conditions thru the Web interface
- > **SNMP Traps:** Provide automated alerts for power and environmental conditions
- > **Input Current Monitor:**
Precisely measure the aggregate current draw (in amps) on each power circuit. On-site verification of the input current with the LED digital display. Remote verification via browser or serial screen.
- > **Power-up Sequencing:** Prevent an in-rush power overload

CW-16V2

High-Density Power Distribution

The Switched CDU's combine remote configuration and management with power distribution and power and environmental monitoring. Reboot a single or dual-power server with one command. Receive SNMP alerts when power or environmental conditions exceed thresholds. Assign users specific access rights to designated outlets or groups.

Only the Switched CDU products provide the flexibility needed for all data centers and remote sites, including power requirements for high-amp, high voltage; UL 60950-1 branch circuit protection; SSL & SSH security; and SNMP-based input current monitoring.

Additional Benefits:



Branch Circuit Protection

The Sentry CDU Family meets the new UL 60950-1 requirement for branch circuit protection.

Attention! The Sentry CDU products meet the above criteria by providing overcurrent protection with UL-listed Bussman SC fuses for each branch circuit.



Input Current Monitoring

The CDU's exclusive True RMS current monitoring is critical to preventing overloads in high-density computing environments. LED digital displays on the CDU enclosure report the input current of each branch circuit.



Temperature and Humidity

The Switched CDU supports two external probes. Each of these probes measure both temperature and humidity. Receive SNMP-based alert notifications when conditions exceed defined thresholds.



Linking (Expansion Modules)

The Switched CDU family has the capability to daisy chain units together. The Expansion Module provides the ability to link two power circuits under one IP address.



Model	Available Input Voltages	Amperage	Available Input Cord	Outlets	Dimensions* (L x W x D)
CW-16V2-C20M CX-16V2-C20M**	208-240V 50/60Hz	20A	IEC 60320/C20 Power Inlet	(16) IEC 60320/C13	49.5 x 1.75 x 2.25 in. (1130 x 44 x 57 mm)
CW-16V2-L30M CX-16V2-L30M**	208-240V 50/60Hz	30A	NEMA L6-30P Cordset 10ft (3m)	(16) IEC 60320/C13	49.5 x 1.75 x 2.25 in. (1130 x 44 x 57 mm)
CW-16VE-C20M CX-16VE-C20M**	230V 50/60Hz	16A	IEC 60320/C20 Power Inlet	(16) IEC 60320/C13	49.5 x 1.75 x 2.25 in. (1130 x 44 x 57 mm)
CW-16VE-P32M CX-16VE-P32M**	230V 50/60Hz	32A	IEC 60309 Cordset 10ft (3m)	(16) IEC 60320/C13	49.5 x 1.75 x 2.25 in. (1130 x 44 x 57 mm)

*Please note that the depths of these enclosures are 3.0" deep at the placement of the fuse retractors

** CX refers to Expansion unit

Additional Features and Specifications

Agency Approvals

- > US & Canada (cTUVus mark) to UL 60950-1:2003 and CAN/CSA 22.2 No. 60950-1-03
- > FCC Class A, Part 15
- > CE
- > EMC to EN 55022 Class A, EN 55024, CISPR 22 Class A

Communications and Security

- > 10/100 BaseT Ethernet
- > HTTP/HTTPS
- > SSLv3/TLSv1
- > SNMPv2
- > SSHv2
- > Telnet
- > LDAPv3
- > LDAPS
- > TACACS+
- > RADIUS
- > RS-232 (Serial)

Branch Circuit Protection


- > Compliant to UL 60950-1

Power Cord Options

- > PTCORD-1 IEC 60320/C19 - NEMA L6-20P , 10'(3m)
- > PTCORD-2 IEC 60320/C19 - Schuko 10'(3m)
- > PTCORD-3 IEC 60320/C19 - IEC 60309 (BS4343, CEE17) 16/20A Blue (UK Commando) 10'(3m)
- > PTCORD-4 IEC 60320/C19 - BS1363 13A (UK) 10'(3m)

Accessories

- > Optional Temperature & Humidity Probe
 - EMTH-1-1 Temperature & Humidity Probe, 10ft (3m)
- > Environmental Monitor
 - EMCU-1-1B allows up to (2) additional temperature & humidity probes, (1) water sensor, (4) dry contact closures, (1) analog-to-digital contact sensor. Includes (1) temperature/humidity probe with unit.
- > SPM (Sentry Power Manager) Appliance:
 - Monitor and Manage multiple Sentry CDU's
 - Monitor and Manage all alarm conditions
 - Reporting and Trending
 - Group or Cluster outlets for reboot and power information



Server Technology

HEADQUARTERS - NORTH AMERICA
 Server Technology, Inc.
 1040 Sandhill Drive
 Reno, NV 89521
 United States
 1.775.284.2000 Tel
 1.775.284.2065 Fax
sales@servertech.com
www.servertech.com
www.servertechblog.com

EMEA
 Server Technology Intl
 United Kingdom
 +44 (0) 1628 509053 Tel
 +44 (0) 1628 509100 Fax
salesintl@servertech.com

APAC
 Server Technology Intl
 37th Floor, Singapore Land Tower
 50 Raffles Place
 Singapore 048623
 +65 (0) 6829 7008 Tel
 +65 (0) 6234 4574 Fax
salesintl@servertech.com