



MAN BOON MANUFACTORY LTD.

PRODUCT TECHNICAL DATA SHEET

Product Code: **T9506-LSNH**

Page: **1 of 1**

Part Number : **20120522-23** Version: **A0**

Date: **2012-5-22**

Dimensional Features


Material Breakdown

Inner Conductor <A>	12 / T0.20(+/-0.008)mm×7	Stranded Tinned copper
Insulation	12 / 1.10(+/-0.13)mm	SPE Insulation (white,red,green,blue,yellow,brown,black×6)
Shield <C>	Al-foil	Al-foil Shield
Drain <D>	T0.20(+/-0.008)mm×7	Stranded Tinned copper
Sheath<F>	7.34 (+/-0.30)mm	Grey LSNH Sheath

Electrical Characteristics

Max.Conductor(A) DC Resistance at 20°C(Ω/100M)	< 9.40
Min.Insulation DC Resistance at 20°C (MΩ*M)	>200
Rated Temperature(°C)	80
Rated Voltage (V)	300

Cable Construction



Physical Characteristics

Minimum Bending Radius(mm)	15×D
Conductor Elongation at Break(%)	>10.0%
Sheath Tensile Strength (N/mm ²)	10.00
Sheath Elongation at Break(%)	100.0%

**Remark: Please contact us if you have more requirements or specifications subject to change, or else in accordance with the standards. **

Please note that the above specification is based on the received requirements and/or our design, we reserve the right to update it to reflect the latest changes.



Man Boon Manufactory Ltd.
Unit 11, 5/F, Wing On Plaza, 62 Mody Road, Tsim Sha Tsui, Kowloon, Hong Kong
Tel: 852- 2558 7578 Fax: 852- 28970314
email: info@manboon.com www.manboon.com



ISO 9001
File A8606



RoHS (2002/95/EC)
Compliant

