



MS-100-SSH

Tapered Pipe-to-Pipe Adapter, adapts 1-1/2 in to 3-1/2 in OD pipe to 4 in to 9 in OD pipe

Dimensions

Mounting Diameter, maximum	88.9 mm		3 1/2 in
Mounting Diameter, minimum	38.1 mm		1 1/2 in
Height	50.8 mm		2.0 in
Length	406.4 mm		16.0 in
Mounting Diameter 2, maximum	228.6 mm		9 in
Mounting Diameter 2, minimum	101.6 mm		4 in
Weight	15.9 kg		35.0 lb
Width	304.8 mm		12.0 in

General Specifications

Product Type	Clamp sets
Tower Taper	Tapered
Includes	Half clamps Threaded rod
Material Type	Hot dip galvanized steel
Mounting	Pipe-to-pipe
Package Quantity	2

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system