



Installation/Operation Instructions

Warranty Information

AT1000	AR2000
AT1000-R3	AR2000-R3
AT1020	AR2020
AT1020-R3	AR2020-R3
AT1025	AR2025
AT1025-R3	AR2025-R3
AR1000	AR2010WDMA
AR1000-R3	AR2010WDMA-R3
AR1030	AR2010WDMB
AR1030-R3	AR2010WDMB-R3



www.ifs.com

888-999-9IFS


AT1000

AUDIO INPUT




AR1000

AUDIO OUTPUT




NOTE:

For an unbalanced connection, tie pin 2 to pin 3 and utilize pins 2 and 3 for the audio input to the AT1000 Series module. Utilize pins 1 and 2 for the audio output from the AR1000 Series module.




AR2000

AUDIO INPUT




AUDIO OUTPUT



NOTE:

For an unbalanced connection, tie pin 2 to pin 3 and utilize pins 1 and 2 for the audio input to the AR2000 Series module. Utilize pins 4 and 5 for the audio output from the AR2000 Series module.




AT1000



A	Power LED
---	-----------


AR1000/AR2000



A	Carrier LED
B	Power LED


NOTE: WITHOUT PROPER FIBER CONNECTION, LED's DO NOT INDICATE CORRECT OPERATIONAL STATUS OF THE UNIT.

AR2000




A	Power Connector
B	Audio Connector
C	Optical In
D	Optical Out

AT1000



A	Power Connector
B	Audio Input Connector
C	Optical Out

AR1000



A	Power Connector
B	Audio Output Connector
C	Optical In

FCC Compliance

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesirable operation.

Changes or modifications not expressly approved by International Fiber Systems, Inc. could void the user's authority to operate the equipment.

NOTE: This equipment has been tested and found to comply with the limits for a Class A digital device, pursuant to Part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference when the equipment is operated in a commercial environment. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instruction manual, may cause harmful interference to radio communications. Operation of this equipment in a residential area is likely to cause harmful interference in which case the user will be required to correct the interference at his own expense.

CLASS 1 LASER PRODUCT
(For purposes of IEC 60825-1)

Complies with FDA Performance Standard for Laser Products
Title 21
Code of Federal Regulations
Subchapter J

Comprehensive Lifetime Warranty



(a) Seller warrants to the original End User that products and any services furnished hereunder will be free from defects in material and workmanship as of the date of delivery, and will conform to Seller's published technical specifications. The foregoing shall apply only to failures to meet said warranties which appear within that period of time during which the Products are installed in their original installation for the original End User and operator of such Products; provided, however, that in the event of product discontinuance, warranty support is limited to five (5) years from the announcement of discontinuance. Notwithstanding the preceding sentence, the duration of the warranty period for products not manufactured by Seller (e.g., fiber optic cabling, test equipment, power supplies or batteries) shall be the warranty period offered by the original manufacturer, if any.

(b) The conditions of any tests shall be mutually agreed upon and Seller shall be notified of, and may be represented at, all tests that may be made. The warranties and remedies set forth herein are conditioned upon (a) proper storage, installation, use and maintenance, and conformance with any applicable recommendations of Seller and (b) Buyer promptly notifying Seller of any defects and, if required, promptly making the product available for correction.

(c) If any product or service fails to meet the foregoing warranties, Seller shall thereupon correct any such failure either at its option,

(i) by repairing any defective or damaged product or parts of the products, or (ii) by making available any necessary repaired or replacement products or parts thereof. Any repaired or replacement part or product shall be warranted for the remaining period of the original Warranty Period. Seller shall pay, or credit Buyer for, the cost of freight for all return shipments of products or parts to Buyer. Where a failure cannot be corrected by Seller's reasonable efforts, the parties will negotiate an equitable adjustment in price.

(d) The preceding paragraph sets forth the exclusive remedies for claims based on defect in or failure of products or services, whether the claim is in contract, indemnity, warranty, tort (including Seller's negligence), strict liability or otherwise and however instituted. Upon the expiration of the warranty period, all such liability shall terminate and BUYER shall have a reasonable time, within thirty days after the warranty period, to give written notice of any defects which appeared during the warranty period. The foregoing warranties are exclusive and in lieu of all other warranties, whether written, oral, implied or statutory. NO IMPLIED OR STATUTORY WARRANTY OF MERCHANTABILITY OR FITNESS FOR PARTICULAR PURPOSE SHALL APPLY. Seller does not warrant any products or services of others which BUYER has designated.

PROPER MOUNTING METHOD FOR THE AT/AR2000



- 1) Locate unit on solid flat horizontal or vertical surface.
- 2) Position unit no closer than 24 inches from any power source or machinery.
- 3) Securely mount unit using (4) four mounting screws (not provided).
- 4) Select the correct voltage requirements for your application, +12VDC or 12VAC.
+12VDC attach black w/white stripe wire to pin 1 and black stripe to pin 2 (GND).
For 12VAC connect brown to pin 1, green to pin 2 and blue to pin 3 from adapter.
- 5) Plug power brick into approved 120v AC outlet.
- 6) Check power LED to insure device is properly powered, LED will illuminate green.

Product Disassembly Instructions for WEEE

Per European Directive 2002/95/EC Waste Electrical and Electronic Equipment

Required Tools:

- One number 2 Phillips (crosstip) screwdriver.**
- One number 2 flat screwdriver.**

For the enclosed box version:

- 1. Locate and remove box cover securement screws. Usually, but not limited to, at least 4 screws.**
- 2. Lift off box top cover.**
- 3. Locate and remove securement screws for printed circuit board.**
- 4. If there are multiple boards to the assembly, continue removing securement screws until none are left.**
- 5. Lift off printed circuit board.**
- 6. Disassembly of box version of product is complete.**

For rack version:

- 1. Locate and remove securement screws for printed circuit board. Usually, but not limited to, at least 4 screws.**
- 2. If there are multiple boards to the assembly, continue removing securement screws until none are left.**
- 3. Lift off printed circuit board(s).**
- 4. Disassembly of rack card version of product is complete.**