# EM3512 Mount

### **WALL MOUNT, EH3512 ENCLOSURE, 24 VAC**

### **Product Features**

- Specifically Designed for EH3512 Enclosures That Use 24 VAC
- Wiring Concealed Inside Mount
- Video, Power Wiring Pre-Installed
- Adjustable Pan/Tilt Head
- Mounts to Wall or Electrical Box
- Pole, Corner Mount Adapters Available



EM3512 MOUNT WITH EH3512 ENCLOSURE


The **EM3512** feedthrough wall mount provides an attractive indoor/outdoor mount for **EH3512** enclosures that use 24 VAC power. Specifically, it is designed for use with the EH3512 enclosure (when a 24 VAC camera is installed), the EH3512-2, and the EH3512-2HD.

All wiring is concealed inside the mount. With the video and power wiring pre-installed, hook-up is easy and simple.

The mount can be attached to a wall surface or a single-gang electrical box. The PA3512 pole mount adapter is available for attaching the mount to a pole, and CM3512 corner mount adapter can be used for installation of the mount on the corner of a building.

An adjustable head allows 320 degrees of horizontal rotation. Tilt adjustment can be up to 90 degrees above or below the horizontal position.

The **EM3512** is constructed of aluminum and has a gray powder coat finish.



NOTE: VALUES IN PARENTHESES ARE CENTIMETERS; ALL OTHERS ARE INCHES.





## **TECHNICAL SPECIFICATIONS**

#### **MODEL**

EM3512 Light duty wall mount with manually

adjustable head

#### **RELATED PRODUCTS**

CM3512 Corner mount adapter for EM3512 mount PA3512 Pole mount adapter for EM3512 mount.

Stainless steel straps supplied. Straps fit 3-inch (7.62 cm) to 8-inch (20.32 cm) diameter

#### **MECHANICAL**

Pan Adjustment 320° Tilt Adjustment ±90°

Locking Method Button screws; 1/8-inch hex wrench supplied

#### **GENERAL**

Environment Indoor/outdoor Construction Aluminum

Finish Gray polyester powder coat

#### **CERTIFICATIONS/PATENTS**

UL/cUL Listed

U.S. Patents D-486,173 S and 6,824,318 B2

#### **MOUNTING METHOD**

Wall mount Mount attaches to wall surface with four 1/4-inch

diameter fasteners. Only two fasteners are required if mounting to a 2x4 stud. Fasteners

are not supplied.

Corner adapter attaches to mounting surface Corner adapter

with four 1/4-inch diameter fasteners (not supplied). Includes hardware to attach mount

to corner adapter

Pole adapter Pole adapter attaches to a pole with two

stainless steel straps (supplied). Straps fit 3-inch (7.62 cm) to 8-inch (20.32 cm) diameter pole. Includes hardware to attach mount to

pole adapter.

Electrical box Electrical box attaches to wall stud with

hardware (not supplied) sufficient to penetrate wall stud 1 inch (2.54 cm). Electrical

box includes screws to attach mount

EH3512 enclosure attaches to mount with two


**Enclosure Mounting** 1/4-20 x 7/8-inch Phillips screws (provided)


Through hole in mounting plate or through Cable Entry

0.5-inch (1.27 cm) conduit opening in bottom


of mount

Weights Unit Shipping 4 lb (1.81 kg) 1.95 lb (0.88 kg) EM3512 2.20 lb (1.00 kg) 4 lb (1.81 kg) CM3512 1.40 lb (0.64 kg) 2 lb (0.91 kg) PA3512









NOTE: VALUES IN PARENTHESES ARE CENTIMETERS; ALL OTHERS ARE INCHES.

