

PT270-24P Pan/Tilt

INDOOR, LIGHT DUTY

Product Features


- “Mini” Pan/Tilt
- Easily Serviced
- Inverted Operation
- Indoor Applications
- External Limit Adjustments
- High Speed Pan Movement ($12^\circ/\text{sec} \pm 1^\circ$)
- 24 VAC Operation
- Capable of Auto/Random Scan Operation When Used with Appropriate Control
- Maximum Load 15 lb (6.8 kg)



The **PT270-24P** “mini” pan/tilt has been carefully engineered to accommodate the lighter, smaller, new generation of CCTV cameras. Small in size, but rugged in operation, the **PT270-24P** measures only 7.75 inches (19.69 cm) high, 8 inches (20.32 cm) wide, and 4.50 inches (11.43 cm) deep. Ideally suited for indoor operation, this pan/tilt can be used in discreet enclosure applications or where space is a consideration.

The **PT270-24P** features aluminum and steel construction and has a long-life 24 VAC motor capable of auto/random scan operation when used with the appropriate Pelco control.

The **PT270-24P** is capable of handling a maximum load of 15 pounds (6.8 kg), making it suitable for use with our EH3010 and other small enclosures.



NOTE: VALUES IN PARENTHESES ARE CENTIMETERS;
ALL OTHERS ARE INCHES.

TECHNICAL SPECIFICATIONS

MODEL

PT270-24P Light duty mini pan/tilt, 24 VAC

ELECTRICAL

Input Voltage	24 VAC, 50/60 Hz	
Power Requirements (Running)		
Pan	0.31 A (7.4 VA)	
Tilt	0.43 A (10.3 VA)	
Connectors	AMP CPC type (mate supplied)	
Motors	2-phase induction type, instantaneous reversing	
Limit Switches	5 A each (pan/tilt); external adjustment	
Conductor Requirements	6 or 7, unshielded (functions: left, right, up, down, motor common, safety ground). No additional conductors for auto scan when used with solid-state control	
Maximum Operating Distances*		
6 Conductors	Cable Size	Maximum Distance
	20 AWG (0.5mm ²)	159 ft (48 m)
	18 AWG (1.0mm ²)	254 ft (77 m)
	16 AWG (1.5mm ²)	403 ft (123 m)
7 Conductors [†]	20 AWG (0.5mm ²)	274 ft (84 m)
	18 AWG (1.0mm ²)	437 ft (133 m)
	16 AWG (1.5mm ²)	694 ft (212 m)

*Distances are calculated with both motors (pan and tilt) running and assuming a 10% voltage drop.

[†]Using 2-wire motor common

MECHANICAL

Pan	0 to 355° movement in horizontal plane
Speed	12°/sec ±1°
Tilt	±90° movement in vertical plane
Speed	3°/sec ±0.5°
Maximum Load	15 lb (6.8 kg) at 2" (5.08 cm) from tilt table surface to center of gravity
Gearing	Chain and sprocket final drive
Bearings	
Pan	Heavy duty ball bearings
Tilt	Oilite bronze bushing
Braking	Friction type
Duty Cycle	50% duty cycle; 30 minute rating

GENERAL

Construction	Aluminum and steel; all internal parts corrosion protected
Finish	Gray polyester powder coat
Environment	Indoor; 32° to 120°F (0° to 49°C)
Unit Weight	9 lb (4.0 kg)
Shipping Weight	10 lb (4.5 kg)

CERTIFICATIONS/RATINGS

- CE, Class B
- UL Listed
- Meets NEMA Type 1 standards

RECOMMENDED CONTROLS

Coaxitron® or Matrix	Refer to individual specification sheets for information.
MPT24DT	Desktop control for 24 VAC pan/tilt.
MPTAZ Series	Desktop pan/tilt and zoom lens control with auto/random scan for 24 VAC pan/tilt.

RECOMMENDED ENCLOSURES

EH3010/EH3014	Small, indoor enclosure
EH4010/EH4014	Small, indoor enclosure
EH3508/EH3512	Small, indoor/outdoor enclosure

RECOMMENDED MOUNTS

PM14	Light duty wall mount; maximum load 20 lb (9.07 kg)
PM105	Medium duty wall mount; maximum load 40 lb (18.14 kg)

Pelco by Schneider Electric

3500 Pelco Way, Clovis, California 93612-5699 United States

USA & Canada Tel (800) 289-9100 Fax (800) 289-9150

International Tel +1 (559) 292-1981 Fax +1 (559) 348-1120

www.pelco.com

Pelco, the Pelco logo, and other trademarks associated with Pelco products referred to in this publication are trademarks of Pelco, Inc. or its affiliates. All other product names and services are the property of their respective companies. Product specifications and availability are subject to change without notice.

©Copyright 2010, Pelco, Inc. All rights reserved.