PP200 Mount

PARAPET MOUNT, LARGE PAN/TILT

Product Features

- Low Cost
- Aluminum Construction
- Supports up to 175 lb (78.75 kg)
- For Use with Pan/Tilt and Environmental Enclosure
- Built-in Pan/Tilt Mounting Arm; Requires Pan/Tilt Adapter
- Mounts to Inside of Parapet; Minimum Parapet Height 18 Inches (45.72 cm)

The **PP200** parapet mount is designed to mount a pan/tilt with environmental enclosure (such as our PT1250P and EH5723-1) to the inside of a parapet.

The **PP200** mounts on the inside of the parapet and can be rotated a full 360 degrees by simply loosening the U-bolts securing the tube assembly. Its unique design allows it to be positioned anywhere on the parapet, including corners.

The **PP200** enables you to install and service equipment safely on rooftops.

Because the pan/tilt mounting arm is built-in, you need only to purchase the appropriate pan/tilt adapter (PA2000 for medium duty pan/tilts or PA2010 for heavy duty pan/tilts).



PP200 SHOWN WITH ENCLOSURE AND PAN/TILT



TECHNICAL SPECIFICATIONS

MODEL

PP200 Parapet mount for pan/tilt with

environmental enclosure; minimum parapet

height 18 inches (45.72 cm)

RELATED PRODUCTS

PA2000 Mount adapter for PT570P, PT570-24P, and

PT680-24P medium duty pan/tilts

PA2010 Mount adapter for PT1250DC, PT1250P,

PT1280P, PT1280SL, and PT1260EX heavy

duty pan/tilts

MECHANICAL

Positioning Adjustment 360°

GENERAL

Construction Aluminum

Finish Gray polyester powder coat

Maximum Load 175 lb (78.75 kg)


Mounting Method Secure PP200 to parapet wall with


16 fasteners (not supplied);

minimum 3/8-inch (10 mm) diameter

recommended

Unit Weight 11.73 lb (5.32 kg) Shipping Weight 15 lb (6.80 kg)





NOTE: VALUES IN PARENTHESES ARE CENTIMETERS; ALL OTHERS ARE INCHES