

Vision with Precision for Demanding Outdoor HD Security

Sony is pleased to introduce a powerful addition to its network HD camera lineup, the SNC-DH180. This vandal-resistant, wide dynamic range camera is designed with a built-in infrared (IR) illuminator. As a dual-stream network camera, it supports H.264, MPEG-4, and JPEG compression formats, and delivers excellent picture quality in HD 720p resolution at 30 frames per second (fps).

Incorporating the new Exmor™ CMOS image sensor from Sony, which is specially designed for surveillance applications, this rugged camera features state-of-the-art image-enhancement technology, View-DR, which demonstrates an extremely wide dynamic range. The SNC-DH180 also features an IR illuminator to deliver quality images even in absolute darkness (0 lx)*. Along with a host of superb features such as DEPA™ Advanced, PoE, a built-in heater, and the Easy Focus/Easy Zoom function, the SNC-DH180 Mini Dome Network Camera is ideal for the most demanding surveillance applications.




* 0 lx requires the use of IR illuminators. IR rays are not visible to the human eye.

Network HD Mini Dome Camera **SNC-DH180**

Preliminary


FEATURES

- Excellent HD*1 picture quality, supporting H.264 at 30 fps **HD**
- The new Exmor CMOS sensor demonstrates high image quality and high sensitivity for surveillance **Exmor**
- Clearly see objects in the dark up to 15 m (49 feet) away with IR Illuminators, which allow the camera to operate in 0 lx*2 lighting conditions *3 (Images 1)
- Superb dynamic range using newly developed View-DR (Visibility enhanced wide Dynamic Range) technology (Images 2) **View-DR**
- The Visibility Enhancer optimizes contrast and makes the subject more visible, even in severe backlight or shadow conditions
- XDNR (eXcellent Dynamic Noise Reduction) technology for clear images without motion blur under low illumination (Images 3)
- Easy Focus function/Easy Zoom function
- DEPA Advanced Intelligent Video and Audio Analytics trigger an alarm, based on user-defined rules
 - ▶ Intelligent Motion Detection
 - ▶ Tamper Alarm
 - ▶ Advanced Audio Detection*4
- Three codecs (H.264, MPEG-4, JPEG) with dual streaming capability
- Power over Ethernet (PoE) capability
- Built-in heater for use in cold
- IP66 Rating
- ONVIF™ Software (Open Network Video Interface Forum) **ONVIF**




Drastic Improvement in Visibility

IR Illuminator
(Images 1)



View-DR (Visibility enhanced wide Dynamic Range)
(Images 2) **View-DR**



OFF ON Actual Images

XDNR (eXcellent Dynamic Noise Reduction)
(Images 3)



OFF ON Actual Images

*1 1280 x 720 *2 0 lx requires the use of IR illuminators. IR rays are not visible to the human eye. *3 When the IR illuminator is activated, the image is in black and white. *4 Available with software version 1.1 or later.

SPECIFICATIONS

SNC-DH180	
Camera	
Image device	1/3 type progressive scan Exmor CMOS sensor
Minimum illumination	TBD
Number of effective pixels (H x V)	Approx. 1.4 Megapixel (1329 x 1049)
Electronic shutter speed	1 s to 1/10000s
Gain control	Auto (3 levels)/Manual
Exposure control	Auto, EV Compensation ^{*1} , Auto Slow Shutter ^{*2}
White balance mode	Auto (ATW, ATW-PRO), Preset, One-push WB, Manual
Lens type	Vari-focal lens
Zoom ratio	Optical 2.9X (x2 Digital Zoom)
Horizontal viewing angle	85.4 to 31.2 degrees
Focal length	f=3.1 to 8.9 mm
F-number	F1.2 (wide), F2.1 (tele)
Minimum objects distance	300 mm
Powered Focus	Yes (Easy Focus)
Powered Zoom	Yes (Easy Zoom)
IR Illuminator	Yes (Wave Length: 850nm (Typical), IR LED: 21pcs)
Camera Features	
Day/Night ^{*3}	Yes
Wide-D	View-DR (approx. 125dB: Theatrical)
Image enhancement	Visibility Enhancer
Noise reduction	XDNR
Image	
Codec image size (H x V)	1280 x 1024, 1280 x 960, 1280 x 800, 1280 x 720, 1024 x 768, 1024 x 576, 800 x 480, 768 x 576, 640 x 480, 640 x 368, 384 x 288, 320 x 240, 320 x 192 (H.264, MPEG-4, JPEG)
Video compression format	H.264, MPEG-4, JPEG
Codec streaming capability	Dual streaming
Maximum frame rate	H.264/MPEG-4/JPEG: 30 fps (1280 x 720)
Audio	
Audio compression	G.711/G.726
Scene Analytics	
Intelligent motion detection	Yes (with built-in Video Motion Filter)
Intelligent object detection	No
Rule filter	Yes
Intelligent audio detection	Yes ^{*4}
Network	
Protocols	IPv4, IPv6, TCP, UDP, ARP, ICMP, IGMP, HTTP, HTTPS, FTP (client/server), SMTP, DHCP, DNS, NTP, RTP/RTCP, RTSP, SNMP (MIB-2)
ONVIF software	Yes
Wireless network	No
Number of clients	10
Authentication	IEEE802.1X
Analog Video Output	
Signal system	NTSC / PAL
Horizontal resolution	600 TV lines
S/N ratio	More than 50dB
Interface	
Ethernet	10BASE-T / 100BASE-TX (RJ-45)
Serial interface	No
Card slots	No
Analog video output	BNC x 1, RCA x 1
Sensor input	x 1
Alarm output	x 2
External microphone input	Mini-jack (Monaural), MIC IN/LINE IN: 2.47VDC plug-in power
Audio line output	Mini-jack (Monaural), Max output level: 1 Vrms
General	
Weight	3 lb 2 oz (1420 g)
Dimensions (ø x H)	6 5/8 x 4 3/4 inches (166 x 119 mm)
Power requirements	PoE ^{*5} , AC24V, DC12V
Power consumption	23 W max.
Operating temperature ^{*6}	-22°F to 122 °F (-30°C to +50°C) (with built in heater)
Storage temperature	-4°F to 140 °F (-20°C to +60°C)
System Requirements	
Operating system	Windows® XP™, Windows Vista™
Processor	Intel Core2 Duo 2 GHz or higher
Memory	1 GB or more
Web browser	Microsoft Internet Explorer® Ver6.0 or 7.0
Supplied Accessories	
CD-ROM (User's Guide, SNC Toolbox), Installation manual, Wire rope, Bracket, BNC cable, I/O cable, Audio cable, M4 shoulder screw, M4 screw x 4, Flyee, L-wrench, B&P Warranty Booklet, Template	


^{*1} VE off mode only. ^{*2} View-DR off mode only. ^{*3} Removable IR Cut Filter.

^{*4} Available with software version 1.1 or later. ^{*5} When used with PoE, SNC-DH180 cannot be used with a heater.

^{*6} Cold start must be greater than -4°F (-20°C) degree.


The SNC-DH180 includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (<http://www.openssl.org/>).

SYSTEM CONFIGURATIONS



DIMENSIONS

Unit: inches (mm)



SONY

Sony Electronics Inc.
1 Sony Drive
Park Ridge, NJ 07656
click: sony.com/security

S-IP2054 (MK10648V1)

© 2010 Sony Electronics Inc. All rights reserved.
Reproduction in whole or in part without written permission is prohibited.
Features and specifications are as of version 1.1 or later and subject to change without notice.
Non-metric weights and measurements are approximate.
Sony, make.believe and the Sony and make.believe logos, DEPA, IPELA and Exmor are trademarks of Sony.
Windows, XP, and Vista are trademarks of Microsoft Corporation.

Printed in USA (1/10)