

RocketPort 16-Port RS-232 Rackmount Interface



Part Number: 99410-7

The RocketPort 16 Rackmount RS-232 Interface RoHS is a separate, rack mountable interface that has sixteen RS-232 RJ45 connections. It is for use with any 16 or 32-Port RocketPort Universal PCI and Universal PCI 550 cards that require an interface, and comes with a 10-foot cable to connect to the board. The chassis, which is 1U height, fits perfectly into a 19" IT equipment rack, and is also stackable. The product is fully compliant with the RoHS directive 2002/95/EC.

System Specifications

Hardware

- **Enclosure** Black Plastic
- **Board Dimensions** 16.75" x 1.75" x 8"
- **Product Weight** 50.6 oz
- **Mounting** 1U 19" Rack

Environmental Specifications

- **Air temperature**
 - **System On** 0 to 60° C
 - **System Off** -20 to 85° C
- **Operating Humidity (non-condensing)** 5% to 95%
- **Altitude** 0 to 10000 Feet
- **MTBF (Mean Time Between Failures)** 42.8 Years

Serial Communications

- **Software Interfaces** RS-232
- **Baud Rate** 300 to 230.4Kbps

Features

- **Manufacturer's Warranty** 5 Years

Export Information

- **Packaged Shipping Weight** 5.06 lbs
- **Package Dimensions** 19.625" x 4" x 14"
- **UPC Code** 7-56727-99410-7
- **Country of Origin** USA
- **ECCN** EAR99
- **Schedule B Number** 8471.80.1000

Regulatory Approvals

- **Emissions** European Standard EN55022
FCC Part 15 Subpart B
Class A limit
CISPR-22
- **Immunity** European Standard EN55024
IEC 1000-4-2/EN61000-4-2: ESD
IEC 1000-4-3/EN61000-4-3: RF
IEC 1000-4-4/EN61000-4-4: Fast Transient
IEC 1000-4-5/EN61000-4-5: Surge
IEC 1000-4-6/EN61000-4-6: Conducted Disturbance
IEC 1000-4-8/EN61000-4-8: Magnetic Field
IEC 1000-4-11/EN61000-4-11: Dips and Voltage Variations
- **Safety** IEC 60950/EN60950
CSA C22.2 No. 60950/UL60950 Third Edition
- **Other Regulatory Approvals**



- **Pinout Diagram**

